

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504782

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504782
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-54)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9551.7 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.16
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 81.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504782

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504782

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92							
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84							
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76							
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69							
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63							
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58							
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53							
8	73	63	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49							
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45							
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51676
5°	51812
10°	51815
15°	51912
20°	51598
25°	51555
30°	51504
35°	45624
40°	34225
45°	21674
50°	9918
55°	1986
60°	731
65°	507
70°	524
75°	533
80°	518
85°	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P1504782

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	605.1	6.3
10°-20°	1742.7	18.2
20°-30°	2656.2	27.8
30°-40°	2811.0	29.4
40°-50°	1469.9	15.4
50°-60°	214.6	2.2
60°-70°	28.9	0.3
70°-80°	17.6	0.2
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5004.0	52.4
0°-40°	7815.0	81.8
0°-60°	9499.5	99.5
0°-90°	9551.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9551.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6372	
5°	6365	605
15°	6183	1743
25°	5762	2656
35°	4608	2811
45°	1890	1470
55°	140	215
65°	26	29
75°	17	18
85°	5	6
90°	0	

TEST NUMBER: P1504782

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	6372.3
2.5°	6357.0
5°	6364.7
7.5°	6341.7
10°	6292.3
12.5°	6248.0
15°	6183.3
17.5°	6088.7
20°	5978.9
22.5°	5868.1
25°	5761.7
27.5°	5639.9
30°	5500.2
32.5°	5124.6
35°	4608.5
37.5°	3976.5
40°	3233.0
42.5°	2511.6
45°	1889.9
47.5°	1313.3
50°	786.1
52.5°	341.5
55°	140.5
57.5°	84.3
60°	45.1
62.5°	33.2
65°	26.4
67.5°	23.8
70°	22.1
72.5°	19.6
75°	17.0
77.5°	13.6
80°	11.1
82.5°	7.7
85°	5.1
87.5°	2.6
90°	0.0

(END OF REPORT)