

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504915

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504915
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12197.4 lumens
Efficiency: N/A
Efficacy: 150.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.09
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 81.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504915

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504915

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	82	77	95	87	81	77	85	80	75	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	85	75	67	62	83	73	67	62	72	66	61	70	65	60	68	63	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	64	56	51	73	63	56	51	61	55	51	60	55	50	59	54	50	48		
8	70	59	52	47	69	58	52	47	57	51	47	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	44	40	62	51	44	40	50	44	40	49	44	40	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64164
5°	64319
10°	64249
15°	63717
20°	62064
25°	60029
30°	56648
35°	46762
40°	34820
45°	23238
50°	14140
55°	11079
60°	9324
65°	9790
70°	10682
75°	11129
80°	11218
85°	10858

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23238 cd/sqm

TEST NUMBER: P1504915

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.1	6.2
10°-20°	2132.3	17.5
20°-30°	3074.1	25.2
30°-40°	2922.1	24.0
40°-50°	1594.6	13.1
50°-60°	716.4	5.9
60°-70°	506.9	4.2
70°-80°	371.0	3.0
80°-90°	128.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5957.5	48.8
0°-40°	8879.6	72.8
0°-60°	11190.6	91.7
0°-90°	12197.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12197.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7912	
5°	7901	751
15°	7589	2132
25°	6709	3074
35°	4724	2922
45°	2026	1595
55°	784	716
65°	510	507
75°	355	371
85°	117	129
90°	0	

TEST NUMBER: P1504915

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (5000K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7912.2
2.5°	7894.3
5°	7901.1
7.5°	7873.0
10°	7802.3
12.5°	7716.3
15°	7589.4
17.5°	7410.5
20°	7191.7
22.5°	6958.3
25°	6708.8
27.5°	6409.8
30°	6049.5
32.5°	5429.5
35°	4723.5
37.5°	4002.1
40°	3289.2
42.5°	2641.9
45°	2026.2
47.5°	1484.5
50°	1120.8
52.5°	924.1
55°	783.6
57.5°	659.2
60°	574.9
62.5°	538.3
65°	510.2
67.5°	484.6
70°	450.5
72.5°	405.4
75°	355.2
77.5°	299.8
80°	240.2
82.5°	179.7
85°	116.7
87.5°	57.1
90°	0.0

(END OF REPORT)