

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504614

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504614
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13756.6 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.29
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 102.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504614

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504614

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82		
3	98	90	84	80	96	89	83	79	86	81	78	84	80	76	81	78	75	73		
4	92	82	76	71	90	81	75	70	79	74	69	77	72	68	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	60	56	65	60	55	64	59	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65422
5°	65584
10°	65728
15°	66097
20°	65956
25°	65949
30°	65920
35°	65585
40°	60237
45°	46893
50°	29460
55°	14666
60°	3348
65°	1514
70°	615
75°	441
80°	503
85°	606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46893 cd/sqm

TEST NUMBER: P1504614

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	718.3	5.2
10°-20°	2079.9	15.1
20°-30°	3183.8	23.1
30°-40°	3837.5	27.9
40°-50°	2909.3	21.1
50°-60°	922.3	6.7
60°-70°	84.0	0.6
70°-80°	15.2	0.1
80°-90°	6.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5981.9	43.5
0°-40°	9819.5	71.4
0°-60°	13651.1	99.2
0°-90°	13756.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13756.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7558	
5°	7548	718
15°	7376	2080
25°	6906	3184
35°	6207	3838
45°	3831	2909
55°	972	922
65°	74	84
75°	13	15
85°	6	6
90°	0	

TEST NUMBER: P1504614

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7558.5
2.5°	7543.3
5°	7548.4
7.5°	7527.1
10°	7478.5
12.5°	7432.0
15°	7376.3
17.5°	7284.1
20°	7160.6
22.5°	7032.1
25°	6905.5
27.5°	6762.8
30°	6595.7
32.5°	6414.5
35°	6207.0
37.5°	5938.7
40°	5331.2
42.5°	4621.6
45°	3830.9
47.5°	2988.6
50°	2187.8
52.5°	1524.7
55°	971.9
57.5°	502.1
60°	193.4
62.5°	121.5
65°	73.9
67.5°	38.5
70°	24.3
72.5°	15.2
75°	13.2
77.5°	12.1
80°	10.1
82.5°	9.1
85°	6.1
87.5°	3.0
90°	0.0

(END OF REPORT)