

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504738

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504738
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15191.6 lumens
Efficiency: N/A
Efficacy: 151.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.13
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 100.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504738

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504738

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80679
5°	80729
10°	80293
15°	79430
20°	77088
25°	74144
30°	69798
35°	62532
40°	51270
45°	40705
50°	33269
55°	19284
60°	10449
65°	8143
70°	7496
75°	8464
80°	9605
85°	10378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40705 cd/sqm

TEST NUMBER: P1504738

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	882.0	5.8
10°-20°	2489.1	16.4
20°-30°	3560.1	23.4
30°-40°	3649.3	24.0
40°-50°	2613.4	17.2
50°-60°	1212.7	8.0
60°-70°	411.5	2.7
70°-80°	263.2	1.7
80°-90°	110.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6931.1	45.6
0°-40°	10580.3	69.6
0°-60°	14406.4	94.8
0°-90°	15191.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15191.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9321	
5°	9292	882
15°	8864	2489
25°	7764	3560
35°	5918	3649
45°	3325	2613
55°	1278	1213
65°	398	412
75°	253	263
85°	104	110
90°	0	

TEST NUMBER: P1504738

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (5000K_L16_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	9321.2
2.5°	9296.6
5°	9291.5
7.5°	9239.2
10°	9135.7
12.5°	9016.9
15°	8864.2
17.5°	8643.9
20°	8369.2
22.5°	8077.2
25°	7763.6
27.5°	7408.0
30°	6983.7
32.5°	6491.9
35°	5918.0
37.5°	5257.0
40°	4537.6
42.5°	3887.9
45°	3325.4
47.5°	2891.9
50°	2470.7
52.5°	1899.9
55°	1277.9
57.5°	769.6
60°	603.6
62.5°	487.8
65°	397.6
67.5°	331.0
70°	296.2
72.5°	271.6
75°	253.1
77.5°	227.5
80°	192.7
82.5°	150.6
85°	104.5
87.5°	54.3
90°	0.0

(END OF REPORT)