

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221204

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221204
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, WIDE DISTRIBUTION.
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8682.4 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.1
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78		
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	60	56	52	51		
9	71	60	54	49	70	60	53	49	59	53	49	58	52	49	57	52	49	47		
10	67	56	50	46	66	56	50	46	55	49	45	54	49	45	53	49	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34377
5°	32891
10°	31506
15°	30471
20°	29104
25°	27825
30°	25649
35°	19690
40°	12846
45°	7097
50°	1710
55°	265
60°	153
65°	147
70°	142
75°	125
80°	92
85°	45

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7097 cd/sqm

TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	596.7	6.9
10°-20°	1734.7	20.0
20°-30°	2646.3	30.5
30°-40°	2487.9	28.7
40°-50°	1080.2	12.4
50°-60°	80.9	0.9
60°-70°	24.3	0.3
70°-80°	18.3	0.2
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	1.1	0.0
140°-150°	1.9	0.0
150°-160°	1.9	0.0
160°-170°	1.5	0.0
170°-180°	0.6	0.0
0°-30°	4977.8	57.3
0°-40°	7465.7	86.0
0°-60°	8626.8	99.4
0°-90°	8675.3	99.9
90°-120°	0.0	0.0
90°-150°	3.1	0.0
90°-180°	7.0	0.1
0°-180°	8682.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6288	
5°	6275	597
15°	6157	1735
25°	5766	2646
35°	4058	2488
45°	1410	1080
55°	49	81
65°	24	24
75°	18	18
85°	5	6
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	2	1
145°	3	2
155°	4	2
165°	5	1
175°	6	1
180°	6	

TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	6288.2
2.5°	6272.1
5°	6274.6
7.5°	6249.3
10°	6212.1
12.5°	6196.1
15°	6157.2
17.5°	6077.8
20°	5978.9
22.5°	5877.6
25°	5766.0
27.5°	5643.5
30°	5320.8
32.5°	4763.2
35°	4057.8
37.5°	3274.6
40°	2609.7
42.5°	1996.4
45°	1410.0
47.5°	828.8
50°	329.5
52.5°	109.0
55°	49.0
57.5°	33.8
60°	27.0
62.5°	25.3
65°	24.5
67.5°	23.7
70°	22.0
72.5°	20.3
75°	17.7
77.5°	14.4
80°	11.8
82.5°	8.4
85°	5.1
87.5°	2.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.8
132.5°	0.8
135°	1.7
137.5°	1.7
140°	2.5
142.5°	2.5
145°	3.4
147.5°	3.4
150°	3.4
152.5°	4.2
155°	4.2
157.5°	4.2
160°	5.1
162.5°	5.1
165°	5.1
167.5°	5.1
170°	5.9
172.5°	5.9
175°	5.9
177.5°	5.9
180°	5.9

TEST NUMBER: P1221204

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-Blak-08 (6500K_L12_Wide_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT