

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221209

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221209
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, NARROW DISTRIBUTION.
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12173.6 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.95
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 122.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95
2	107	102	98	95	105	101	97	94	97	94	91	94	92	89	92	89	88
3	102	95	90	86	100	94	89	85	91	87	84	88	85	82	86	83	81
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75
5	91	82	76	72	89	81	76	71	79	75	71	78	73	70	76	72	69
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52
10	70	60	54	50	69	59	53	50	58	53	49	58	53	49	57	52	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65345
5°	61978
10°	57564
15°	52802
20°	47153
25°	40751
30°	32530
35°	22865
40°	13657
45°	4786
50°	4153
55°	602
60°	168
65°	157
70°	146
75°	125
80°	93
85°	52

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 5279 cd/sqm

TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1113.3	9.1
10°-20°	2983.6	24.5
20°-30°	3836.8	31.5
30°-40°	2924.7	24.0
40°-50°	1045.4	8.6
50°-60°	207.9	1.7
60°-70°	25.6	0.2
70°-80°	18.6	0.2
80°-90°	6.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	1.3	0.0
140°-150°	2.7	0.0
150°-160°	3.1	0.0
160°-170°	2.6	0.0
170°-180°	1.0	0.0
0°-30°	7933.7	65.2
0°-40°	10858.4	89.2
0°-60°	12111.8	99.5
0°-90°	12162.8	99.9
90°-120°	0.0	0.0
90°-150°	4.0	0.0
90°-180°	11.0	0.1
0°-180°	12173.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11953	
5°	11824	###
15°	10670	2984
25°	8445	3837
35°	4712	2925
45°	951	1045
55°	112	208
65°	26	26
75°	18	19
85°	6	6
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	1	1
145°	5	3
155°	7	3
165°	10	3
175°	11	1
180°	11	

TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	11953.0
2.5°	11898.4
5°	11823.6
7.5°	11634.8
10°	11349.9
12.5°	11040.0
15°	10669.6
17.5°	10211.3
20°	9686.6
22.5°	9116.7
25°	8444.7
27.5°	7715.8
30°	6748.2
32.5°	5707.0
35°	4712.1
37.5°	3750.4
40°	2774.5
42.5°	1722.7
45°	951.0
47.5°	1034.1
50°	800.2
52.5°	378.7
55°	111.6
57.5°	49.9
60°	29.7
62.5°	27.3
65°	26.1
67.5°	23.7
70°	22.6
72.5°	20.2
75°	17.8
77.5°	15.4
80°	11.9
82.5°	9.5
85°	5.9
87.5°	3.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	1.2
132.5°	1.2
135°	1.2
137.5°	2.4
140°	2.4
142.5°	3.6
145°	4.7
147.5°	4.7
150°	5.9
152.5°	5.9
155°	7.1
157.5°	7.1
160°	8.3
162.5°	8.3
165°	9.5
167.5°	9.5
170°	10.7
172.5°	10.7
175°	10.7
177.5°	10.7
180°	10.7

TEST NUMBER: P1221209

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (6500K_L18_Narrow_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT