

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504609

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504609
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11257.1 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.12
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 83
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504609

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504609

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	71	64	59	80	70	63	58	68	62	58	67	61	57	65	61	57	55		
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43		
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64911
5°	64990
10°	64691
15°	63967
20°	61890
25°	59169
30°	54970
35°	48538
40°	39486
45°	30603
50°	24150
55°	12388
60°	4326
65°	1874
70°	557
75°	284
80°	294
85°	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30603 cd/sqm

TEST NUMBER: P1504609

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	710.3	6.3
10°-20°	2003.4	17.8
20°-30°	2837.0	25.2
30°-40°	2838.6	25.2
40°-50°	1963.6	17.4
50°-60°	784.4	7.0
60°-70°	105.7	0.9
70°-80°	10.6	0.1
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5550.7	49.3
0°-40°	8389.3	74.5
0°-60°	11137.3	98.9
0°-90°	11257.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11257.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7500	
5°	7480	710
15°	7139	2003
25°	6196	2837
35°	4594	2839
45°	2500	1964
55°	821	784
65°	92	106
75°	8	11
85°	3	4
90°	0	

TEST NUMBER: P1504609

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	7499.5
2.5°	7482.5
5°	7480.0
7.5°	7442.7
10°	7360.5
12.5°	7266.5
15°	7138.6
17.5°	6953.9
20°	6719.2
22.5°	6469.3
25°	6195.6
27.5°	5883.0
30°	5500.1
32.5°	5068.8
35°	4593.6
37.5°	4070.8
40°	3494.7
42.5°	2970.3
45°	2500.1
47.5°	2120.6
50°	1793.5
52.5°	1333.5
55°	820.9
57.5°	385.5
60°	249.9
62.5°	159.3
65°	91.5
67.5°	44.9
70°	22.0
72.5°	10.2
75°	8.5
77.5°	7.6
80°	5.9
82.5°	5.1
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)