

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504749

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504749
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15773.3 lumens
Efficiency: N/A
Efficacy: 153.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.31 / 1.3
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 102.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504749

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504749

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50		
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	46	40	36	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68314
5°	68513
10°	68718
15°	69200
20°	69266
25°	69468
30°	69715
35°	69607
40°	64401
45°	51280
50°	34489
55°	20594
60°	10059
65°	9124
70°	9480
75°	11140
80°	13274
85°	14976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51280 cd/sqm

TEST NUMBER: P1504749

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	750.6	4.8
10°-20°	2178.8	13.8
20°-30°	3354.7	21.3
30°-40°	4073.4	25.8
40°-50°	3190.5	20.2
50°-60°	1270.2	8.1
60°-70°	451.7	2.9
70°-80°	346.7	2.2
80°-90°	156.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6284.1	39.8
0°-40°	10357.5	65.7
0°-60°	14818.2	93.9
0°-90°	15773.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15773.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7893	
5°	7886	751
15°	7722	2179
25°	7274	3355
35°	6588	4073
45°	4189	3190
55°	1365	1270
65°	446	452
75°	333	347
85°	151	157
90°	0	

TEST NUMBER: P1504749

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (6500K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7892.6
2.5°	7877.4
5°	7885.5
7.5°	7867.3
10°	7818.7
12.5°	7776.2
15°	7722.5
17.5°	7636.5
20°	7520.0
22.5°	7395.5
25°	7274.0
27.5°	7136.3
30°	6975.4
32.5°	6794.1
35°	6587.6
37.5°	6307.2
40°	5699.8
42.5°	4984.0
45°	4189.3
47.5°	3349.0
50°	2561.3
52.5°	1912.4
55°	1364.7
57.5°	891.9
60°	581.1
62.5°	503.2
65°	445.5
67.5°	398.9
70°	374.6
72.5°	353.3
75°	333.1
77.5°	305.7
80°	266.3
82.5°	216.7
85°	150.8
87.5°	74.9
90°	0.0

(END OF REPORT)