

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504616

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504616
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14997.7 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.97
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 123.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504616

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504616

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	50	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	46	67	57	50	46	56	50	45	55	49	45	54	49	45	44			
10	65	53	47	42	63	53	47	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103436
5°	102456
10°	98980
15°	94103
20°	87221
25°	78009
30°	66502
35°	54800
40°	45610
45°	39403
50°	35005
55°	19649
60°	7980
65°	3363
70°	891
75°	354
80°	409
85°	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 39483 cd/sqm

TEST NUMBER: P1504616

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1108.8	7.4
10°-20°	2936.6	19.6
20°-30°	3724.2	24.8
30°-40°	3265.8	21.8
40°-50°	2535.0	16.9
50°-60°	1215.0	8.1
60°-70°	193.3	1.3
70°-80°	14.7	0.1
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7769.6	51.8
0°-40°	11035.3	73.6
0°-60°	14785.4	98.6
0°-90°	14997.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14997.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11950	
5°	11792	###
15°	10502	2937
25°	8168	3724
35°	5186	3266
45°	3219	2535
55°	1302	1215
65°	164	193
75°	11	15
85°	4	4
90°	0	

TEST NUMBER: P1504616

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (6500K_L18_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	11950.4
2.5°	11885.9
5°	11792.1
7.5°	11585.6
10°	11261.8
12.5°	10906.4
15°	10501.7
17.5°	10026.5
20°	9469.3
22.5°	8854.6
25°	8168.3
27.5°	7430.5
30°	6653.9
32.5°	5892.5
35°	5186.3
37.5°	4575.1
40°	4036.7
42.5°	3541.6
45°	3219.0
47.5°	3081.8
50°	2599.6
52.5°	2000.1
55°	1302.1
57.5°	674.5
60°	461.0
62.5°	296.8
65°	164.2
67.5°	80.9
70°	35.2
72.5°	14.1
75°	10.6
77.5°	9.4
80°	8.2
82.5°	5.9
85°	3.5
87.5°	2.3
90°	0.0

(END OF REPORT)