

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505476

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505476
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-116)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23488.7 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.11
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505476

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505476

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92							
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84							
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76							
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69							
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63							
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58							
7	78	67	60	56	76	66	60	55	65	59	55	64	59	55	63	58	54	53							
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49							
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45							
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103757
5°	103786
10°	103348
15°	102879
20°	101766
25°	100049
30°	95390
35°	80955
40°	60762
45°	42172
50°	24209
55°	7798
60°	3593
65°	1003
70°	648
75°	684
80°	730
85°	724

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42172 cd/sqm

TEST NUMBER: P1505476

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1541.0	6.6
10°-20°	4396.1	18.7
20°-30°	6517.7	27.7
30°-40°	6406.4	27.3
40°-50°	3630.4	15.5
50°-60°	857.7	3.7
60°-70°	99.2	0.4
70°-80°	29.2	0.1
80°-90°	11.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12454.7	53.0
0°-40°	18861.0	80.3
0°-60°	23349.2	99.4
0°-90°	23488.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23488.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16286	
5°	16228	###
15°	15598	4396
25°	14232	6518
35°	10409	6406
45°	4680	3630
55°	702	858
65°	66	99
75°	28	29
85°	10	11
90°	0	

TEST NUMBER: P1505476

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	16285.5
2.5°	16250.8
5°	16228.0
7.5°	16136.6
10°	15974.8
12.5°	15803.0
15°	15597.5
17.5°	15334.4
20°	15009.7
22.5°	14660.2
25°	14232.2
27.5°	13679.2
30°	12966.3
32.5°	11826.4
35°	10408.6
37.5°	8869.6
40°	7305.8
42.5°	5914.7
45°	4680.5
47.5°	3544.7
50°	2442.5
52.5°	1373.2
55°	702.0
57.5°	464.7
60°	282.0
62.5°	139.0
65°	66.5
67.5°	41.7
70°	34.8
72.5°	31.8
75°	27.8
77.5°	23.8
80°	19.9
82.5°	14.9
85°	9.9
87.5°	6.0
90°	0.0

(END OF REPORT)