

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504391

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504391
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16675.5 lumens
Efficiency: N/A
Efficacy: 135.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 123.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504391

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504391

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109635
5°	108849
10°	105690
15°	101224
20°	94678
25°	85930
30°	74475
35°	62427
40°	52349
45°	45045
50°	41086
55°	24562
60°	14057
65°	10191
70°	8897
75°	10060
80°	11786
85°	12910

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 45672 cd/sqm

TEST NUMBER: P1504391

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1118.2	6.7
10°-20°	2995.5	18.0
20°-30°	3887.1	23.3
30°-40°	3516.2	21.1
40°-50°	2773.2	16.6
50°-60°	1461.3	8.8
60°-70°	496.5	3.0
70°-80°	297.9	1.8
80°-90°	129.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8000.8	48.0
0°-40°	11517.1	69.1
0°-60°	15751.6	94.5
0°-90°	16675.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16675.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12004	
5°	11873	###
15°	10706	2996
25°	8527	3887
35°	5599	3516
45°	3488	2773
55°	1543	1461
65°	472	496
75°	285	298
85°	123	129
90°	0	

TEST NUMBER: P1504391

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (6500K_L18_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	12004.4
2.5°	11946.9
5°	11873.0
7.5°	11692.4
10°	11396.7
12.5°	11075.3
15°	10705.8
17.5°	10255.3
20°	9741.5
22.5°	9165.5
25°	8527.3
27.5°	7811.7
30°	7062.1
32.5°	6318.4
35°	5599.2
37.5°	4955.2
40°	4390.9
42.5°	3887.7
45°	3487.6
47.5°	3378.5
50°	2891.7
52.5°	2262.9
55°	1542.6
57.5°	967.8
60°	769.6
62.5°	604.1
65°	471.6
67.5°	384.8
70°	333.2
72.5°	303.8
75°	285.1
77.5°	260.4
80°	224.1
82.5°	178.3
85°	123.2
87.5°	62.2
90°	0.0

(END OF REPORT)