

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504569

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504569
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-48)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14858.5 lumens
Efficiency: N/A
Efficacy: 145.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.17
Luminous Opening: Circular (Dia: 1.29' x H: 0')
CIE Type: Direct

Input Watts (W): 102.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504569

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504569

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	95	90	85	91	87	83	88	85	81	85	82	80	78		
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	67	59	54	76	66	59	53	64	58	53	63	57	52	61	56	52	50		
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46		
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42		
9	65	53	45	41	63	52	45	40	51	45	40	50	44	40	49	44	40	38		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67644
5°	67686
10°	67548
15°	68214
20°	68428
25°	68939
30°	69054
35°	60659
40°	46551
45°	32954
50°	20144
55°	13325
60°	12990
65°	14306
70°	16000
75°	17383
80°	17721
85°	16890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32954 cd/sqm

TEST NUMBER: P1504569

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	779.5	5.2
10°-20°	2263.1	15.2
20°-30°	3504.7	23.6
30°-40°	3708.7	25.0
40°-50°	2203.1	14.8
50°-60°	906.1	6.1
60°-70°	727.4	4.9
70°-80°	567.3	3.8
80°-90°	198.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6547.3	44.1
0°-40°	10255.9	69.0
0°-60°	13365.1	89.9
0°-90°	14858.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14858.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8235	
5°	8208	779
15°	8021	2263
25°	7606	3505
35°	6049	3709
45°	2837	2203
55°	930	906
65°	736	727
75°	548	567
85°	179	199
90°	0	

TEST NUMBER: P1504569

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (6500K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8234.8
2.5°	8213.5
5°	8208.5
7.5°	8155.8
10°	8098.1
12.5°	8065.7
15°	8021.2
17.5°	7938.1
20°	7827.8
22.5°	7720.5
25°	7606.1
27.5°	7468.4
30°	7280.1
32.5°	6741.5
35°	6049.0
37.5°	5244.2
40°	4341.1
42.5°	3553.5
45°	2836.7
47.5°	2180.7
50°	1576.3
52.5°	1104.5
55°	930.4
57.5°	847.4
60°	790.7
62.5°	763.3
65°	736.0
67.5°	706.6
70°	666.2
72.5°	612.5
75°	547.7
77.5°	468.7
80°	374.6
82.5°	276.4
85°	179.2
87.5°	87.1
90°	0.0

(END OF REPORT)