

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505118

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505118
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-105)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22970.2 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.21
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505118

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505118

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62		
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51		
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47		
9	68	57	50	45	67	56	49	45	55	49	45	54	49	45	53	48	44	43		
10	64	53	46	42	63	52	46	41	51	45	41	50	45	41	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94459
5°	94514
10°	94584
15°	95179
20°	95340
25°	95790
30°	95978
35°	87004
40°	72215
45°	51154
50°	28584
55°	7102
60°	2027
65°	893
70°	755
75°	871
80°	953
85°	911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51154 cd/sqm

TEST NUMBER: P1505118

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1342.2	5.8
10°-20°	3889.0	16.9
20°-30°	5998.5	26.1
30°-40°	6586.4	28.7
40°-50°	4182.5	18.2
50°-60°	854.2	3.7
60°-70°	69.1	0.3
70°-80°	34.9	0.2
80°-90°	13.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11229.8	48.9
0°-40°	17816.2	77.6
0°-60°	22852.8	99.5
0°-90°	22970.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	22970.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14160	
5°	14114	###
15°	13782	3889
25°	13014	5998
35°	10684	6586
45°	5422	4182
55°	611	854
65°	57	69
75°	34	35
85°	12	13
90°	0	

TEST NUMBER: P1505118

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (3000K_L32_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	14159.8
2.5°	14131.9
5°	14114.1
7.5°	14051.5
10°	13963.2
12.5°	13879.8
15°	13781.5
17.5°	13626.6
20°	13430.0
22.5°	13224.4
25°	13013.9
27.5°	12765.7
30°	12459.9
32.5°	11662.6
35°	10683.6
37.5°	9542.8
40°	8292.7
42.5°	6883.8
45°	5422.2
47.5°	4076.8
50°	2754.3
52.5°	1588.6
55°	610.6
57.5°	257.2
60°	151.9
62.5°	86.4
65°	56.6
67.5°	42.7
70°	38.7
72.5°	36.7
75°	33.8
77.5°	29.8
80°	24.8
82.5°	18.9
85°	11.9
87.5°	6.0
90°	0.0

(END OF REPORT)