

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505251

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505251
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-110)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE
SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28291.6 lumens
Efficiency: N/A
Efficacy: 141.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.13
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505251

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1505251

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57		
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113389
5°	113343
10°	112919
15°	112897
20°	112412
25°	111473
30°	107266
35°	91678
40°	70866
45°	51866
50°	33901
55°	20093
60°	17050
65°	16315
70°	18243
75°	20295
80°	22278
85°	23789

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51866 cd/sqm

TEST NUMBER: P1505251

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1607.3	5.7
10°-20°	4611.8	16.3
20°-30°	6938.1	24.5
30°-40°	6947.2	24.6
40°-50°	4268.3	15.1
50°-60°	1719.7	6.1
60°-70°	1049.2	3.7
70°-80°	820.3	2.9
80°-90°	329.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13157.2	46.5
0°-40°	20104.4	71.1
0°-60°	26092.4	92.2
0°-90°	28291.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	28291.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16998	
5°	16926	###
15°	16347	4612
25°	15145	6938
35°	11258	6947
45°	5498	4268
55°	1728	1720
65°	1034	1049
75°	787	820
85°	311	330
90°	0	

TEST NUMBER: P1505251

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3000K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	16997.5
2.5°	16954.8
5°	16926.0
7.5°	16825.7
10°	16669.8
12.5°	16521.9
15°	16347.1
17.5°	16122.7
20°	15834.8
22.5°	15527.0
25°	15144.7
27.5°	14624.4
30°	13925.4
32.5°	12709.1
35°	11257.5
37.5°	9695.7
40°	8137.8
42.5°	6732.9
45°	5497.7
47.5°	4375.7
50°	3266.6
52.5°	2258.8
55°	1727.6
57.5°	1478.4
60°	1277.9
62.5°	1115.0
65°	1033.6
67.5°	981.0
70°	935.3
72.5°	870.8
75°	787.4
77.5°	691.1
80°	579.9
82.5°	453.8
85°	310.8
87.5°	156.9
90°	0.0

(END OF REPORT)