

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505431

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505431
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-98)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29376.0 lumens
Efficiency: N/A
Efficacy: 147.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.19
Luminous Opening: Circular (Dia: 1.38' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505431

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505431

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	66	61	82	73	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	67	60	54	77	66	59	54	65	59	54	63	58	53	62	57	53	51		
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42		
9	65	53	46	41	63	52	46	41	51	45	41	50	45	40	49	44	40	39		
10	61	49	42	38	60	49	42	37	48	42	37	47	41	37	46	41	37	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118022
5°	118080
10°	117726
15°	117378
20°	116795
25°	115833
30°	112590
35°	104397
40°	86831
45°	67650
50°	52194
55°	36152
60°	17038
65°	13361
70°	11456
75°	12887
80°	14905
85°	16722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 67650 cd/sqm

TEST NUMBER: P1505431

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1560.4	5.3
10°-20°	4466.7	15.2
20°-30°	6729.2	22.9
30°-40°	7320.6	24.9
40°-50°	5217.4	17.8
50°-60°	2576.8	8.8
60°-70°	805.7	2.7
70°-80°	487.4	1.7
80°-90°	211.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12756.4	43.4
0°-40°	20076.9	68.3
0°-60°	27871.1	94.9
0°-90°	29376.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	29376.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16479	
5°	16425	###
15°	15831	4467
25°	14658	6729
35°	11941	7321
45°	6679	5217
55°	2895	2577
65°	788	806
75°	466	487
85°	204	212
90°	0	

TEST NUMBER: P1505431

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (3000K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	16479.2
2.5°	16446.4
5°	16424.6
7.5°	16344.1
10°	16188.2
12.5°	16021.4
15°	15830.8
17.5°	15596.5
20°	15324.4
22.5°	15011.7
25°	14658.2
27.5°	14208.4
30°	13614.6
32.5°	12881.9
35°	11940.6
37.5°	10678.6
40°	9287.6
42.5°	7930.3
45°	6679.2
47.5°	5604.9
50°	4684.5
52.5°	3799.8
55°	2895.3
57.5°	1991.8
60°	1189.5
62.5°	962.1
65°	788.4
67.5°	644.4
70°	547.1
72.5°	502.4
75°	465.7
77.5°	423.0
80°	361.4
82.5°	287.9
85°	203.5
87.5°	106.2
90°	0.0

(END OF REPORT)