

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505473

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505473
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-116)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19516.9 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.11
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 159.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505473

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505473

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92							
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84							
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76							
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69							
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63							
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58							
7	78	67	60	56	76	66	60	55	65	59	55	64	59	55	63	58	54	53							
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49							
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45							
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86212
5°	86236
10°	85872
15°	85483
20°	84558
25°	83131
30°	79260
35°	67266
40°	50487
45°	35041
50°	20116
55°	6479
60°	2986
65°	834
70°	538
75°	569
80°	605
85°	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35041 cd/sqm

TEST NUMBER: P1505473

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1280.4	6.6
10°-20°	3652.7	18.7
20°-30°	5415.5	27.7
30°-40°	5323.1	27.3
40°-50°	3016.5	15.5
50°-60°	712.7	3.7
60°-70°	82.4	0.4
70°-80°	24.3	0.1
80°-90°	9.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10348.6	53.0
0°-40°	15671.7	80.3
0°-60°	19400.9	99.4
0°-90°	19516.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	19516.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13532	
5°	13484	###
15°	12960	3653
25°	11826	5416
35°	8648	5323
45°	3889	3017
55°	583	713
65°	55	82
75°	23	24
85°	8	9
90°	0	

TEST NUMBER: P1505473

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-BLAK-PS (3000K_L24_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	13531.7
2.5°	13502.8
5°	13483.9
7.5°	13408.0
10°	13273.5
12.5°	13130.8
15°	12960.0
17.5°	12741.4
20°	12471.6
22.5°	12181.2
25°	11825.6
27.5°	11366.1
30°	10773.7
32.5°	9826.6
35°	8648.5
37.5°	7369.8
40°	6070.4
42.5°	4914.5
45°	3889.1
47.5°	2945.3
50°	2029.5
52.5°	1141.0
55°	583.3
57.5°	386.1
60°	234.3
62.5°	115.5
65°	55.3
67.5°	34.7
70°	28.9
72.5°	26.4
75°	23.1
77.5°	19.8
80°	16.5
82.5°	12.4
85°	8.3
87.5°	5.0
90°	0.0

(END OF REPORT)