

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505611

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505611
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-122)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28406.8 lumens
Efficiency: N/A
Efficacy: 142.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505611

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505611

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	77	72	67	75	70	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	54	63	58	54	52		
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110362
5°	110447
10°	110035
15°	109690
20°	108740
25°	106890
30°	102022
35°	87527
40°	68177
45°	51092
50°	34258
55°	19366
60°	16068
65°	14729
70°	16165
75°	17475
80°	18323
85°	18436

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51092 cd/sqm

TEST NUMBER: P1505611

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1640.0	5.8
10°-20°	4688.0	16.5
20°-30°	6963.7	24.5
30°-40°	6948.5	24.5
40°-50°	4383.9	15.4
50°-60°	1769.6	6.2
60°-70°	1000.0	3.5
70°-80°	739.5	2.6
80°-90°	273.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13291.7	46.8
0°-40°	20240.2	71.3
0°-60°	26393.7	92.9
0°-90°	28406.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	28406.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17322	
5°	17270	###
15°	16630	4688
25°	15205	6964
35°	11254	6949
45°	5670	4384
55°	1744	1770
65°	977	1000
75°	710	739
85°	252	274
90°	0	

TEST NUMBER: P1505611

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	17322.1
2.5°	17288.4
5°	17269.5
7.5°	17174.2
10°	17008.4
12.5°	16838.6
15°	16630.1
17.5°	16357.0
20°	16038.3
22.5°	15660.0
25°	15205.3
27.5°	14611.5
30°	13867.8
32.5°	12695.2
35°	11253.5
37.5°	9713.5
40°	8197.4
42.5°	6853.0
45°	5670.5
47.5°	4548.5
50°	3456.3
52.5°	2387.9
55°	1743.5
57.5°	1478.4
60°	1261.0
62.5°	1078.3
65°	977.0
67.5°	919.4
70°	867.8
72.5°	798.3
75°	709.9
77.5°	609.6
80°	499.4
82.5°	379.3
85°	252.2
87.5°	124.1
90°	0.0

(END OF REPORT)