

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504947

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504947
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-81)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26719.9 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 1.3 / 1.3 / 1.29
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 196.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504947

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504947

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	70	58	51	46	68	57	50	45	56	50	45	55	49	45	54	49	45	43		
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105331
5°	105432
10°	105571
15°	106221
20°	106446
25°	106918
30°	107265
35°	106568
40°	96523
45°	76457
50°	51871
55°	30114
60°	8923
65°	2882
70°	987
75°	595
80°	718
85°	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 76457 cd/sqm

TEST NUMBER: P1504947

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1361.7	5.1
10°-20°	3946.5	14.8
20°-30°	6088.4	22.8
30°-40°	7299.1	27.3
40°-50°	5633.0	21.1
50°-60°	2142.8	8.0
60°-70°	211.3	0.8
70°-80°	26.2	0.1
80°-90°	11.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11396.5	42.7
0°-40°	18695.6	70.0
0°-60°	26471.4	99.1
0°-90°	26719.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	26719.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14355	
5°	14314	###
15°	13983	3946
25°	13206	6088
35°	11897	7299
45°	7368	5633
55°	2354	2143
65°	166	211
75°	21	26
85°	11	11
90°	0	

TEST NUMBER: P1504947

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (3500K_L32_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	14355
2.5°	14326
5°	14314
7.5°	14261
10°	14169
12.5°	14087
15°	13983
17.5°	13826
20°	13632
22.5°	13417
25°	13206
27.5°	12957
30°	12660
32.5°	12313
35°	11897
37.5°	11094
40°	10077
42.5°	8804
45°	7368
47.5°	5919
50°	4544
52.5°	3369
55°	2354
57.5°	1405
60°	608
62.5°	280
65°	166
67.5°	91
70°	46
72.5°	28
75°	21
77.5°	19
80°	17
82.5°	15
85°	11
87.5°	6
90°	0

(END OF REPORT)