

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505613

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505613
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-123)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29221.6 lumens
Efficiency: N/A
Efficacy: 146.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.25
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 199.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505613

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505613

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78		
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55		
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96565
5°	96902
10°	97355
15°	97967
20°	98407
25°	99246
30°	100057
35°	93875
40°	80960
45°	61988
50°	41127
55°	21517
60°	16599
65°	17049
70°	19069
75°	20971
80°	21713
85°	20761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61988 cd/sqm

TEST NUMBER: P1505613

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1443.0	4.9
10°-20°	4194.6	14.4
20°-30°	6511.6	22.3
30°-40°	7440.6	25.5
40°-50°	5293.8	18.1
50°-60°	2009.0	6.9
60°-70°	1132.1	3.9
70°-80°	882.1	3.0
80°-90°	314.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12149.2	41.6
0°-40°	19589.8	67.0
0°-60°	26892.6	92.0
0°-90°	29221.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	29221.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15157	
5°	15152	###
15°	14853	4195
25°	14118	6512
35°	12070	7441
45°	6880	5294
55°	1937	2009
65°	1131	1132
75°	852	882
85°	284	315
90°	0	

TEST NUMBER: P1505613

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3000K_L32_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	15156.6
2.5°	15142.7
5°	15151.7
7.5°	15121.9
10°	15048.4
12.5°	14966.0
15°	14852.8
17.5°	14698.9
20°	14514.2
22.5°	14323.6
25°	14118.0
27.5°	13878.8
30°	13600.7
32.5°	12962.3
35°	12069.7
37.5°	10981.5
40°	9734.4
42.5°	8348.3
45°	6879.8
47.5°	5480.8
50°	4149.3
52.5°	2947.9
55°	1937.1
57.5°	1457.6
60°	1302.7
62.5°	1195.5
65°	1130.9
67.5°	1079.3
70°	1023.7
72.5°	948.2
75°	851.9
77.5°	733.8
80°	591.8
82.5°	438.9
85°	284.0
87.5°	138.0
90°	0.0

(END OF REPORT)