

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505257

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505257
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-110)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE
SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23661.5 lumens
Efficiency: N/A
Efficacy: 150.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.13
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 157.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505257

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1505257

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57		
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94832
5°	94794
10°	94439
15°	94421
20°	94015
25°	93230
30°	89711
35°	76674
40°	59269
45°	43378
50°	28353
55°	16805
60°	14258
65°	13646
70°	15256
75°	16972
80°	18632
85°	19893

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43378 cd/sqm

TEST NUMBER: P1505257

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1344.3	5.7
10°-20°	3857.0	16.3
20°-30°	5802.6	24.5
30°-40°	5810.2	24.6
40°-50°	3569.8	15.1
50°-60°	1438.2	6.1
60°-70°	877.5	3.7
70°-80°	686.1	2.9
80°-90°	275.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11003.9	46.5
0°-40°	16814.2	71.1
0°-60°	21822.2	92.2
0°-90°	23661.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23661.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14216	
5°	14156	###
15°	13672	3857
25°	12666	5803
35°	9415	5810
45°	4598	3570
55°	1445	1438
65°	864	878
75°	658	686
85°	260	276
90°	0	

TEST NUMBER: P1505257

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	14215.7
2.5°	14180.0
5°	14155.9
7.5°	14072.1
10°	13941.7
12.5°	13817.9
15°	13671.8
17.5°	13484.1
20°	13243.3
22.5°	12985.9
25°	12666.2
27.5°	12231.0
30°	11646.4
32.5°	10629.2
35°	9415.1
37.5°	8108.9
40°	6806.0
42.5°	5631.0
45°	4598.0
47.5°	3659.6
50°	2732.0
52.5°	1889.2
55°	1444.9
57.5°	1236.5
60°	1068.7
62.5°	932.5
65°	864.5
67.5°	820.4
70°	782.2
72.5°	728.3
75°	658.5
77.5°	578.0
80°	485.0
82.5°	379.5
85°	259.9
87.5°	131.2
90°	0.0

(END OF REPORT)