

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505258

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505258
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-109)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE
SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23002.4 lumens
Efficiency: N/A
Efficacy: 146.0 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.03
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 157.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505258

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1505258

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53		
7	75	64	57	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	67	55	48	44	65	55	48	43	54	48	43	53	47	43	52	47	43	41		
10	63	52	45	40	62	51	45	40	50	44	40	49	44	40	49	43	40	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106559
5°	106460
10°	105728
15°	104090
20°	99096
25°	91757
30°	79867
35°	64691
40°	52218
45°	41278
50°	30163
55°	18813
60°	14348
65°	12727
70°	13977
75°	15282
80°	16143
85°	16847

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41278 cd/sqm

TEST NUMBER: P1505258

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1508.2	6.6
10°-20°	4216.4	18.3
20°-30°	5666.7	24.6
30°-40°	4994.2	21.7
40°-50°	3399.7	14.8
50°-60°	1533.4	6.7
60°-70°	830.8	3.6
70°-80°	617.2	2.7
80°-90°	235.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11391.3	49.5
0°-40°	16385.5	71.2
0°-60°	21318.6	92.7
0°-90°	23002.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23002.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15974	
5°	15898	###
15°	15072	4216
25°	12466	5667
35°	7944	4994
45°	4375	3400
55°	1618	1533
65°	806	831
75°	593	617
85°	220	236
90°	0	

TEST NUMBER: P1505258

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (3500K_L24_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	15973.7
2.5°	15928.8
5°	15898.1
7.5°	15787.7
10°	15608.3
12.5°	15386.6
15°	15071.9
17.5°	14586.9
20°	13959.1
22.5°	13278.2
25°	12466.1
27.5°	11482.9
30°	10368.4
32.5°	9107.9
35°	7943.7
37.5°	6908.1
40°	5996.4
42.5°	5179.2
45°	4375.4
47.5°	3718.6
50°	2906.4
52.5°	1954.8
55°	1617.6
57.5°	1334.5
60°	1075.4
62.5°	898.5
65°	806.3
67.5°	755.7
70°	716.6
72.5°	663.5
75°	592.9
77.5°	513.2
80°	420.2
82.5°	323.0
85°	220.1
87.5°	112.9
90°	0.0

(END OF REPORT)