

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505619

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505619
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-123)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24439.3 lumens
Efficiency: N/A
Efficacy: 155.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.25
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 157.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505619

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505619

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78		
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55		
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80761
5°	81044
10°	81422
15°	81934
20°	82302
25°	83004
30°	83682
35°	78512
40°	67711
45°	51844
50°	34397
55°	17996
60°	13883
65°	14258
70°	15947
75°	17539
80°	18158
85°	17361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51844 cd/sqm

TEST NUMBER: P1505619

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1206.8	4.9
10°-20°	3508.1	14.4
20°-30°	5445.9	22.3
30°-40°	6222.9	25.5
40°-50°	4427.5	18.1
50°-60°	1680.2	6.9
60°-70°	946.8	3.9
70°-80°	737.8	3.0
80°-90°	263.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10160.9	41.6
0°-40°	16383.8	67.0
0°-60°	22491.5	92.0
0°-90°	24439.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24439.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12676	
5°	12672	###
15°	12422	3508
25°	11808	5446
35°	10094	6223
45°	5754	4427
55°	1620	1680
65°	946	947
75°	712	738
85°	238	263
90°	0	

TEST NUMBER: P1505619

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L24_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	12676.1
2.5°	12664.5
5°	12672.0
7.5°	12647.1
10°	12585.6
12.5°	12516.7
15°	12422.0
17.5°	12293.3
20°	12138.9
22.5°	11979.4
25°	11807.5
27.5°	11607.4
30°	11374.9
32.5°	10840.9
35°	10094.4
37.5°	9184.3
40°	8141.3
42.5°	6982.1
45°	5753.9
47.5°	4583.8
50°	3470.3
52.5°	2465.5
55°	1620.1
57.5°	1219.0
60°	1089.5
62.5°	999.8
65°	945.8
67.5°	902.7
70°	856.1
72.5°	793.0
75°	712.5
77.5°	613.7
80°	494.9
82.5°	367.0
85°	237.5
87.5°	115.4
90°	0.0

(END OF REPORT)