

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505623

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505623
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-122)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 33257.5 lumens
Efficiency: N/A
Efficacy: 141.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 235.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505623

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505623

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	77	72	67	75	70	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	54	63	58	54	52		
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129207
5°	129306
10°	128824
15°	128421
20°	127309
25°	125142
30°	119444
35°	102472
40°	79818
45°	59816
50°	40108
55°	22674
60°	18811
65°	17243
70°	18926
75°	20459
80°	21453
85°	21587

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 59816 cd/sqm

TEST NUMBER: P1505623

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1920.0	5.8
10°-20°	5488.5	16.5
20°-30°	8152.9	24.5
30°-40°	8135.0	24.5
40°-50°	5132.5	15.4
50°-60°	2071.8	6.2
60°-70°	1170.8	3.5
70°-80°	865.7	2.6
80°-90°	320.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	15561.4	46.8
0°-40°	23696.4	71.3
0°-60°	30900.7	92.9
0°-90°	33257.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	33257.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20280	
5°	20218	###
15°	19470	5488
25°	17802	8153
35°	13175	8135
45°	6639	5132
55°	2041	2072
65°	1144	1171
75°	831	866
85°	295	320
90°	0	

TEST NUMBER: P1505623

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	20280.0
2.5°	20240.5
5°	20218.4
7.5°	20106.8
10°	19912.7
12.5°	19713.9
15°	19469.8
17.5°	19150.1
20°	18777.0
22.5°	18334.1
25°	17801.7
27.5°	17106.5
30°	16235.9
32.5°	14863.0
35°	13175.1
37.5°	11372.2
40°	9597.1
42.5°	8023.2
45°	6638.7
47.5°	5325.2
50°	4046.5
52.5°	2795.7
55°	2041.3
57.5°	1730.9
60°	1476.3
62.5°	1262.4
65°	1143.8
67.5°	1076.4
70°	1016.0
72.5°	934.6
75°	831.1
77.5°	713.7
80°	584.7
82.5°	444.1
85°	295.3
87.5°	145.3
90°	0.0

(END OF REPORT)