

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505139

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505139
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-105)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28012.8 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.21
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 231.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505139

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505139

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62		
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51		
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47		
9	68	57	50	45	67	56	49	45	55	49	45	54	49	45	53	48	44	43		
10	64	53	46	42	63	52	46	41	51	45	41	50	45	41	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115195
5°	115262
10°	115348
15°	116073
20°	116270
25°	116819
30°	117047
35°	106103
40°	88069
45°	62384
50°	34859
55°	8661
60°	2472
65°	1089
70°	921
75°	1062
80°	1164
85°	1110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 62384 cd/sqm

TEST NUMBER: P1505139

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1636.9	5.8
10°-20°	4742.8	16.9
20°-30°	7315.3	26.1
30°-40°	8032.3	28.7
40°-50°	5100.6	18.2
50°-60°	1041.7	3.7
60°-70°	84.2	0.3
70°-80°	42.5	0.2
80°-90°	16.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13695.0	48.9
0°-40°	21727.3	77.6
0°-60°	27869.7	99.5
0°-90°	28012.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	28012.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17268	
5°	17212	###
15°	16807	4743
25°	15871	7315
35°	13029	8032
45°	6613	5101
55°	745	1042
65°	69	84
75°	41	43
85°	14	16
90°	0	

TEST NUMBER: P1505139

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (4000K_L36_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	17268.2
2.5°	17234.3
5°	17212.5
7.5°	17136.2
10°	17028.4
12.5°	16926.7
15°	16806.9
17.5°	16618.0
20°	16378.2
22.5°	16127.6
25°	15870.9
27.5°	15568.1
30°	15195.2
32.5°	14222.9
35°	13028.9
37.5°	11637.7
40°	10113.2
42.5°	8395.0
45°	6612.6
47.5°	4971.8
50°	3358.9
52.5°	1937.4
55°	744.7
57.5°	313.6
60°	185.3
62.5°	105.3
65°	69.0
67.5°	52.1
70°	47.2
72.5°	44.8
75°	41.2
77.5°	36.3
80°	30.3
82.5°	23.0
85°	14.5
87.5°	7.3
90°	0.0

(END OF REPORT)