

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505624

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505624
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-121)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 32082.5 lumens
Efficiency: N/A
Efficacy: 136.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.99
Luminous Opening: Circular (Dia: 1.47' x H: 0')
CIE Type: Direct

Input Watts (W): 235.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505624

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505624

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72		
4	91	82	75	69	89	80	74	69	78	73	68	76	71	67	74	70	66	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	67	55	48	44	66	55	48	44	54	48	43	53	47	43	52	47	43	42		
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149781
5°	149461
10°	147707
15°	142674
20°	133015
25°	118915
30°	101023
35°	82799
40°	68952
45°	56684
50°	43956
55°	26483
60°	19670
65°	16455
70°	17626
75°	18630
80°	18638
85°	18268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 56684 cd/sqm

TEST NUMBER: P1505624

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2213.6	6.9
10°-20°	6038.9	18.8
20°-30°	7704.8	24.0
30°-40°	6713.6	20.9
40°-50°	4920.3	15.3
50°-60°	2292.2	7.1
60°-70°	1137.7	3.5
70°-80°	787.3	2.5
80°-90°	274.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	15957.4	49.7
0°-40°	22671.0	70.7
0°-60°	29883.5	93.1
0°-90°	32082.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	32082.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23509	
5°	23370	###
15°	21631	6039
25°	16916	7705
35°	10646	6714
45°	6291	4920
55°	2384	2292
65°	1092	1138
75°	757	787
85°	250	274
90°	0	

TEST NUMBER: P1505624

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-06-WHGL-PS (3500K_L36_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	23509.3
2.5°	23440.7
5°	23369.8
7.5°	23168.7
10°	22831.6
12.5°	22328.2
15°	21630.8
17.5°	20690.4
20°	19618.6
22.5°	18370.1
25°	16915.9
27.5°	15321.0
30°	13732.0
32.5°	12117.3
35°	10645.7
37.5°	9398.4
40°	8290.6
42.5°	7275.7
45°	6291.1
47.5°	5679.7
50°	4434.7
52.5°	2994.5
55°	2384.2
57.5°	1950.6
60°	1543.7
62.5°	1252.0
65°	1091.5
67.5°	1010.2
70°	946.2
72.5°	862.5
75°	756.8
77.5°	637.0
80°	508.0
82.5°	379.0
85°	249.9
87.5°	124.4
90°	0.0

(END OF REPORT)