

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504952

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504952
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21799.5 lumens
Efficiency: N/A
Efficacy: 140.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 155.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504952

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504952

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74		
4	93	84	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56		
7	76	66	58	54	75	65	58	53	63	57	53	62	57	53	61	56	52	51		
8	72	61	54	49	71	60	54	49	59	53	49	58	52	49	57	52	48	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119701
5°	119366
10°	118120
15°	115027
20°	107744
25°	97157
30°	82073
35°	67253
40°	55304
45°	46262
50°	42362
55°	27663
60°	10977
65°	5389
70°	1401
75°	414
80°	507
85°	581

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 46431 cd/sqm

TEST NUMBER: P1504952

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1535.7	7.0
10°-20°	4226.4	19.4
20°-30°	5451.0	25.0
30°-40°	4722.0	21.7
40°-50°	3572.4	16.4
50°-60°	1923.3	8.8
60°-70°	336.8	1.5
70°-80°	24.8	0.1
80°-90°	7.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11213.1	51.4
0°-40°	15935.1	73.1
0°-60°	21430.8	98.3
0°-90°	21799.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	21799.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16313	
5°	16206	###
15°	15142	4226
25°	12000	5451
35°	7508	4722
45°	4458	3572
55°	2162	1923
65°	310	337
75°	15	25
85°	7	7
90°	0	

TEST NUMBER: P1504952

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (4000K_L24_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	16313.3
2.5°	16255.7
5°	16205.8
7.5°	16070.8
10°	15853.3
12.5°	15557.5
15°	15142.2
17.5°	14531.7
20°	13798.3
22.5°	12978.1
25°	12000.4
27.5°	10871.5
30°	9686.7
32.5°	8565.5
35°	7507.9
37.5°	6570.7
40°	5773.7
42.5°	5078.9
45°	4458.1
47.5°	4275.0
50°	3711.0
52.5°	2964.6
55°	2162.4
57.5°	1336.2
60°	748.0
62.5°	503.0
65°	310.4
67.5°	154.8
70°	65.3
72.5°	27.5
75°	14.6
77.5°	13.8
80°	12.0
82.5°	9.5
85°	6.9
87.5°	3.4
90°	0.0

(END OF REPORT)