

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505447

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)

Issue Date: 7/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1505447  
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-97)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)  
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, NARROW DISTRIBUTION  
LIGHT LEVEL 1 - 24,000 LUMENS  
Light Source:  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 24400.1 lumens  
Efficiency: N/A  
Efficacy: 156.7 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 1.01  
Luminous Opening: Circular (Dia: 1.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 155.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1505447

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)

### Luminous Intensity Polar Plot





TEST NUMBER: P1505447

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99  | 97  | 98  | 96  | 94  | 94  | 93  | 92  | 90  |  |  |
| 2   | 104 | 98  | 93  | 88  | 102 | 96  | 91  | 87  | 93  | 89  | 85  | 90  | 86  | 83  | 87  | 84  | 82  | 80  |  |  |
| 3   | 97  | 89  | 83  | 77  | 95  | 87  | 82  | 77  | 85  | 80  | 76  | 82  | 78  | 74  | 80  | 76  | 73  | 71  |  |  |
| 4   | 91  | 81  | 74  | 69  | 89  | 80  | 73  | 68  | 78  | 72  | 67  | 75  | 71  | 67  | 73  | 69  | 66  | 64  |  |  |
| 5   | 85  | 74  | 67  | 62  | 83  | 73  | 66  | 61  | 71  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 59  | 58  |  |  |
| 6   | 79  | 68  | 61  | 56  | 78  | 67  | 60  | 55  | 66  | 60  | 55  | 64  | 59  | 54  | 63  | 58  | 54  | 52  |  |  |
| 7   | 74  | 63  | 56  | 50  | 73  | 62  | 55  | 50  | 61  | 55  | 50  | 60  | 54  | 50  | 58  | 53  | 49  | 48  |  |  |
| 8   | 70  | 58  | 51  | 46  | 69  | 58  | 51  | 46  | 57  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 45  | 44  |  |  |
| 9   | 66  | 54  | 47  | 42  | 65  | 54  | 47  | 42  | 53  | 47  | 42  | 52  | 46  | 42  | 51  | 46  | 42  | 40  |  |  |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 44  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 48  | 43  | 39  | 37  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 120091 |
| 5°  | 119993 |
| 10° | 118798 |
| 15° | 115676 |
| 20° | 108716 |
| 25° | 98391  |
| 30° | 83989  |
| 35° | 69664  |
| 40° | 58521  |
| 45° | 50117  |
| 50° | 47373  |
| 55° | 34130  |
| 60° | 17809  |
| 65° | 13347  |
| 70° | 10298  |
| 75° | 11063  |
| 80° | 12517  |
| 85° | 13074  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $47.5^\circ$

Luminance: 51161 cd/sqm

TEST NUMBER: P1505447

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 1581.9  | 6.5       |
| 10°-20°   | 4359.2  | 17.9      |
| 20°-30°   | 5661.7  | 23.2      |
| 30°-40°   | 5015.7  | 20.6      |
| 40°-50°   | 3970.9  | 16.3      |
| 50°-60°   | 2414.4  | 9.9       |
| 60°-70°   | 804.7   | 3.3       |
| 70°-80°   | 421.3   | 1.7       |
| 80°-90°   | 170.2   | 0.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 11602.9 | 47.6      |
| 0°-40°    | 16618.6 | 68.1      |
| 0°-60°    | 23004.0 | 94.3      |
| 0°-90°    | 24400.1 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 24400.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 16768 |      |
| 5°  | 16691 | ###  |
| 15° | 15601 | 4359 |
| 25° | 12451 | 5662 |
| 35° | 7968  | 5016 |
| 45° | 4948  | 3971 |
| 55° | 2733  | 2414 |
| 65° | 788   | 805  |
| 75° | 400   | 421  |
| 85° | 159   | 170  |
| 90° | 0     |      |

TEST NUMBER: P1505447

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K\_L24\_Narrow\_120V)

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 16768.1 |
| 2.5°  | 16732.0 |
| 5°    | 16690.7 |
| 7.5°  | 16561.8 |
| 10°   | 16335.6 |
| 12.5° | 16044.2 |
| 15°   | 15601.3 |
| 17.5° | 14991.7 |
| 20°   | 14264.3 |
| 22.5° | 13430.3 |
| 25°   | 12451.0 |
| 27.5° | 11322.0 |
| 30°   | 10156.1 |
| 32.5° | 9029.8  |
| 35°   | 7967.9  |
| 37.5° | 7038.4  |
| 40°   | 6259.5  |
| 42.5° | 5578.5  |
| 45°   | 4948.2  |
| 47.5° | 4826.1  |
| 50°   | 4251.8  |
| 52.5° | 3508.0  |
| 55°   | 2733.4  |
| 57.5° | 1894.2  |
| 60°   | 1243.3  |
| 62.5° | 1000.0  |
| 65°   | 787.6   |
| 67.5° | 607.0   |
| 70°   | 491.8   |
| 72.5° | 437.6   |
| 75°   | 399.8   |
| 77.5° | 360.3   |
| 80°   | 303.5   |
| 82.5° | 235.6   |
| 85°   | 159.1   |
| 87.5° | 79.1    |
| 90°   | 0.0     |

(END OF REPORT)