

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505143

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505143
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-104)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24491.6 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.14
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 195.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505143

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505143

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92							
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84							
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76							
4	94	85	79	74	92	84	78	73	82	77	73	80	75	72	78	74	71	69							
5	88	78	72	67	86	77	71	66	76	70	66	74	69	65	72	68	65	63							
6	83	72	66	61	81	72	65	60	70	64	60	69	63	60	67	63	59	58							
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53							
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	54	50	48							
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45							
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110611
5°	110455
10°	109968
15°	109694
20°	109054
25°	108564
30°	106226
35°	91502
40°	69654
45°	46330
50°	24793
55°	7060
60°	3150
65°	982
70°	739
75°	814
80°	891
85°	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46330 cd/sqm

TEST NUMBER: P1505143

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1566.3	6.4
10°-20°	4479.0	18.3
20°-30°	6774.8	27.7
30°-40°	6912.9	28.2
40°-50°	3832.2	15.6
50°-60°	792.2	3.2
60°-70°	87.8	0.4
70°-80°	33.1	0.1
80°-90°	13.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12820.1	52.3
0°-40°	19733.0	80.6
0°-60°	24357.5	99.5
0°-90°	24491.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24491.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16581	
5°	16495	###
15°	15883	4479
25°	14749	6775
35°	11236	6913
45°	4911	3832
55°	607	792
65°	62	88
75°	32	33
85°	13	13
90°	0	

TEST NUMBER: P1505143

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	16581.0
2.5°	16527.2
5°	16494.6
7.5°	16398.7
10°	16234.3
12.5°	16066.7
15°	15883.3
17.5°	15632.5
20°	15361.7
22.5°	15070.8
25°	14749.4
27.5°	14330.0
30°	13790.4
32.5°	12652.3
35°	11235.9
37.5°	9690.0
40°	7998.6
42.5°	6379.9
45°	4910.9
47.5°	3613.6
50°	2389.0
52.5°	1299.4
55°	607.0
57.5°	391.0
60°	236.1
62.5°	117.0
65°	62.2
67.5°	42.2
70°	37.9
72.5°	34.8
75°	31.6
77.5°	28.5
80°	23.2
82.5°	17.9
85°	12.6
87.5°	6.3
90°	0.0

(END OF REPORT)