

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505144

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505144
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-103)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24049.9 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 195.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505144

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505144

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92							
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84							
3	100	93	87	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77							
4	94	86	80	75	92	85	79	74	82	77	74	80	76	73	78	75	72	70							
5	89	79	73	68	87	78	72	68	77	71	67	75	70	66	73	69	66	64							
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59							
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54							
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50							
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	51	48	47							
10	67	56	49	45	65	55	49	45	55	49	45	54	49	45	53	48	45	43							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129718
5°	129536
10°	128443
15°	126063
20°	119340
25°	109309
30°	93807
35°	73788
40°	57311
45°	42591
50°	27451
55°	11583
60°	4682
65°	1081
70°	638
75°	678
80°	730
85°	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42591 cd/sqm

TEST NUMBER: P1505144

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1834.1	7.6
10°-20°	5102.2	21.2
20°-30°	6744.2	28.0
30°-40°	5702.2	23.7
40°-50°	3508.6	14.6
50°-60°	1008.7	4.2
60°-70°	112.1	0.5
70°-80°	27.4	0.1
80°-90°	10.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13680.5	56.9
0°-40°	19382.7	80.6
0°-60°	23900.0	99.4
0°-90°	24049.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24049.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19445	
5°	19344	###
15°	18253	5102
25°	14851	6744
35°	9061	5702
45°	4515	3509
55°	996	1009
65°	68	112
75°	26	27
85°	10	10
90°	0	

TEST NUMBER: P1505144

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-BLAK-PS (5000K_L32_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	19445.3
2.5°	19389.4
5°	19344.1
7.5°	19197.6
10°	18961.6
12.5°	18689.7
15°	18253.4
17.5°	17606.3
20°	16810.7
22.5°	15903.4
25°	14850.6
27.5°	13576.5
30°	12178.1
32.5°	10558.3
35°	9060.8
37.5°	7746.7
40°	6581.2
42.5°	5529.4
45°	4514.6
47.5°	3674.7
50°	2645.1
52.5°	1426.9
55°	995.9
57.5°	653.4
60°	350.9
62.5°	161.2
65°	68.5
67.5°	37.9
70°	32.7
72.5°	29.5
75°	26.3
77.5°	22.1
80°	19.0
82.5°	13.7
85°	9.5
87.5°	5.3
90°	0.0

(END OF REPORT)