

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505090

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505090
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29541.3 lumens
Efficiency: N/A
Efficacy: 152.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.02
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 194.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505090

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505090

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	78	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	60	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52		
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146777
5°	146660
10°	145458
15°	142584
20°	134728
25°	123187
30°	106012
35°	88191
40°	73187
45°	62408
50°	57912
55°	40882
60°	21555
65°	16027
70°	12604
75°	13781
80°	16256
85°	17958

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 62408 cd/sqm

TEST NUMBER: P1505090

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1887.9	6.4
10°-20°	5244.4	17.8
20°-30°	6919.6	23.4
30°-40°	6178.1	20.9
40°-50°	4786.2	16.2
50°-60°	2840.8	9.6
60°-70°	947.0	3.2
70°-80°	513.5	1.7
80°-90°	223.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	14051.9	47.6
0°-40°	20230.0	68.5
0°-60°	27857.1	94.3
0°-90°	29541.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	29541.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20003	
5°	19911	###
15°	18770	5244
25°	15216	6920
35°	9845	6178
45°	6014	4786
55°	3196	2841
65°	923	947
75°	486	514
85°	213	224
90°	0	

TEST NUMBER: P1505090

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (4000K_L32_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	20003.3
2.5°	19960.5
5°	19911.3
7.5°	19757.7
10°	19522.5
12.5°	19213.0
15°	18769.8
17.5°	18092.4
20°	17254.0
22.5°	16333.0
25°	15215.5
27.5°	13924.4
30°	12512.1
32.5°	11147.9
35°	9845.4
37.5°	8652.6
40°	7640.7
42.5°	6789.7
45°	6014.1
47.5°	5692.1
50°	5073.2
52.5°	4158.5
55°	3195.7
57.5°	2183.8
60°	1468.8
62.5°	1170.8
65°	923.1
67.5°	717.1
70°	587.5
72.5°	526.9
75°	486.1
77.5°	445.3
80°	384.7
82.5°	306.3
85°	213.3
87.5°	109.8
90°	0.0

(END OF REPORT)