

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505267

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505267
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-109)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23817.0 lumens
Efficiency: N/A
Efficacy: 153.0 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.03
Luminous Opening: Circular (Dia: 1.43' x H: 0')
CIE Type: Direct

Input Watts (W): 155.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505267

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505267

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53		
7	75	64	57	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	67	55	48	44	65	55	48	43	54	48	43	53	47	43	52	47	43	41		
10	63	52	45	40	62	51	45	40	50	44	40	49	44	40	49	43	40	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110333
5°	110231
10°	109473
15°	107777
20°	102606
25°	95006
30°	82696
35°	66982
40°	54067
45°	42740
50°	31232
55°	19480
60°	14856
65°	13179
70°	14472
75°	15823
80°	16715
85°	17444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42740 cd/sqm

TEST NUMBER: P1505267

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1561.6	6.6
10°-20°	4365.7	18.3
20°-30°	5867.4	24.6
30°-40°	5171.1	21.7
40°-50°	3520.2	14.8
50°-60°	1587.7	6.7
60°-70°	860.2	3.6
70°-80°	639.1	2.7
80°-90°	244.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11794.7	49.5
0°-40°	16965.8	71.2
0°-60°	22073.6	92.7
0°-90°	23817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16539	
5°	16461	###
15°	15606	4366
25°	12908	5867
35°	8225	5171
45°	4530	3520
55°	1675	1588
65°	835	860
75°	614	639
85°	228	244
90°	0	

TEST NUMBER: P1505267

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (4000K_L24_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	16539.4
2.5°	16493.0
5°	16461.2
7.5°	16346.8
10°	16161.1
12.5°	15931.5
15°	15605.7
17.5°	15103.5
20°	14453.5
22.5°	13748.4
25°	12907.5
27.5°	11889.5
30°	10735.7
32.5°	9430.5
35°	8225.0
37.5°	7152.8
40°	6208.7
42.5°	5362.7
45°	4530.4
47.5°	3850.3
50°	3009.4
52.5°	2024.0
55°	1674.9
57.5°	1381.7
60°	1113.5
62.5°	930.3
65°	834.9
67.5°	782.4
70°	742.0
72.5°	687.0
75°	613.9
77.5°	531.4
80°	435.1
82.5°	334.5
85°	227.9
87.5°	116.9
90°	0.0

(END OF REPORT)