

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505452

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505452
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-98)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 35825.0 lumens
Efficiency: N/A
Efficacy: 154.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.19
Luminous Opening: Circular (Dia: 1.38' x H: 0')
CIE Type: Direct

Input Watts (W): 231.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505452

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505452

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	66	61	82	73	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	67	60	54	77	66	59	54	65	59	54	63	58	53	62	57	53	51		
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42		
9	65	53	46	41	63	52	46	41	51	45	41	50	45	40	49	44	40	39		
10	61	49	42	38	60	49	42	37	48	42	37	47	41	37	46	41	37	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143931
5°	144002
10°	143571
15°	143145
20°	142435
25°	141262
30°	137307
35°	127315
40°	105893
45°	82501
50°	63653
55°	44088
60°	20778
65°	16292
70°	13971
75°	15715
80°	18180
85°	20395

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 82501 cd/sqm

TEST NUMBER: P1505452

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1903.0	5.3
10°-20°	5447.3	15.2
20°-30°	8206.4	22.9
30°-40°	8927.6	24.9
40°-50°	6362.8	17.8
50°-60°	3142.4	8.8
60°-70°	982.6	2.7
70°-80°	594.4	1.7
80°-90°	258.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	15556.8	43.4
0°-40°	24484.4	68.3
0°-60°	33989.6	94.9
0°-90°	35825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	35825.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20097	
5°	20030	###
15°	19306	5447
25°	17876	8206
35°	14562	8928
45°	8146	6363
55°	3531	3142
65°	961	983
75°	568	594
85°	248	258
90°	0	

TEST NUMBER: P1505452

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (4000K_L36_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	20096.8
2.5°	20056.8
5°	20030.2
7.5°	19932.1
10°	19742.0
12.5°	19538.6
15°	19306.1
17.5°	19020.3
20°	18688.5
22.5°	18307.1
25°	17876.1
27.5°	17327.5
30°	16603.4
32.5°	15709.8
35°	14561.9
37.5°	13022.9
40°	11326.5
42.5°	9671.2
45°	8145.5
47.5°	6835.4
50°	5712.9
52.5°	4634.0
55°	3530.9
57.5°	2429.0
60°	1450.6
62.5°	1173.3
65°	961.4
67.5°	785.9
70°	667.2
72.5°	612.7
75°	567.9
77.5°	515.8
80°	440.8
82.5°	351.2
85°	248.2
87.5°	129.6
90°	0.0

(END OF REPORT)