

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505456

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505456
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-97)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, CONIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24646.5 lumens
Efficiency: N/A
Efficacy: 157.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 1.01
Luminous Opening: Circular (Dia: 1.38' x H: 0')
CIE Type: Direct

Input Watts (W): 156.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505456

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1505456

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	54	63	58	54	52		
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121304
5°	121205
10°	119998
15°	116845
20°	109813
25°	99384
30°	84838
35°	70367
40°	59111
45°	50624
50°	47851
55°	34474
60°	17988
65°	13481
70°	10403
75°	11176
80°	12645
85°	13205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 51678 cd/sqm

TEST NUMBER: P1505456

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1597.9	6.5
10°-20°	4403.2	17.9
20°-30°	5718.9	23.2
30°-40°	5066.4	20.6
40°-50°	4011.0	16.3
50°-60°	2438.8	9.9
60°-70°	812.8	3.3
70°-80°	425.6	1.7
80°-90°	172.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11720.0	47.6
0°-40°	16786.4	68.1
0°-60°	23236.2	94.3
0°-90°	24646.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24646.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16937	
5°	16859	###
15°	15759	4403
25°	12577	5719
35°	8048	5066
45°	4998	4011
55°	2761	2439
65°	796	813
75°	404	426
85°	161	172
90°	0	

TEST NUMBER: P1505456

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-B-04-WHGL-PS (5000K_L24_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	16937.4
2.5°	16900.9
5°	16859.2
7.5°	16729.0
10°	16500.5
12.5°	16206.1
15°	15758.9
17.5°	15143.1
20°	14408.3
22.5°	13565.9
25°	12576.7
27.5°	11436.3
30°	10258.7
32.5°	9120.9
35°	8048.3
37.5°	7109.5
40°	6322.6
42.5°	5634.8
45°	4998.2
47.5°	4874.9
50°	4294.7
52.5°	3543.5
55°	2760.9
57.5°	1913.3
60°	1255.8
62.5°	1010.1
65°	795.5
67.5°	613.2
70°	496.8
72.5°	442.1
75°	403.9
77.5°	363.9
80°	306.6
82.5°	238.0
85°	160.7
87.5°	79.9
90°	0.0

(END OF REPORT)