

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221383

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221383
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 2436 LIGHT ENGINE, BLACK SHADE, NARROW DISTRIBUTION.
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18317.1 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98
Luminous Opening: Vertical Cylinder (Dia: 1.54' x H: 0.71')
CIE Type: Direct

Input Watts (W): 154.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221383

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221383

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		85
3	101	94	89	84	99	93	88	84	90	86	82		88	84	81		78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		66
6	85	75	69	64	83	74	68	64	73	68	64		71	67	63		61
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		57
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		52
9	72	62	55	51	71	61	55	51	60	54	51		59	54	50		49
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91934
5°	87405
10°	82527
15°	77082
20°	69534
25°	60701
30°	48653
35°	35435
40°	24474
45°	13591
50°	6769
55°	2570
60°	426
65°	208
70°	195
75°	170
80°	135
85°	79

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13591 cd/sqm

TEST NUMBER: P1221383

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1504.4	8.2
10°-20°	4175.8	22.8
20°-30°	5501.9	30.0
30°-40°	4450.7	24.3
40°-50°	2114.5	11.5
50°-60°	495.2	2.7
60°-70°	39.5	0.2
70°-80°	25.3	0.1
80°-90°	9.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11182.0	61.0
0°-40°	15632.7	85.3
0°-60°	18242.4	99.6
0°-90°	18317.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18317.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15943	
5°	15873	###
15°	14936	4176
25°	12143	5502
35°	7096	4451
45°	2642	2114
55°	469	495
65°	34	40
75°	24	25
85°	9	10
90°	0	

TEST NUMBER: P1221383

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	15943.2
2.5°	15898.0
5°	15873.0
7.5°	15745.8
10°	15548.4
12.5°	15308.3
15°	14936.1
17.5°	14401.6
20°	13744.1
22.5°	13008.9
25°	12143.1
27.5°	11092.5
30°	9775.0
32.5°	8385.7
35°	7095.8
37.5°	5930.6
40°	4847.4
42.5°	3783.4
45°	2641.6
47.5°	1642.8
50°	1280.6
52.5°	916.8
55°	469.3
57.5°	194.1
60°	74.4
62.5°	41.8
65°	34.3
67.5°	31.8
70°	30.1
72.5°	26.8
75°	24.3
77.5°	20.9
80°	17.6
82.5°	13.4
85°	9.2
87.5°	5.0
90°	0.0

TEST NUMBER: P1221383

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L24_Narrow_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.91	3.98	3.27	4.30	4.61	2.91	3.98	3.27	4.30	4.61
	3H	2.87	3.82	3.26	4.15	4.52	2.87	3.82	3.26	4.15	4.52
	4H	2.87	3.74	3.27	4.09	4.48	2.87	3.74	3.27	4.09	4.48
	6H	2.85	3.65	3.27	4.02	4.42	2.85	3.65	3.27	4.02	4.42
	8H	2.83	3.58	3.26	3.97	4.38	2.83	3.58	3.26	3.97	4.38
	12H	2.80	3.51	3.23	3.89	4.32	2.80	3.51	3.23	3.89	4.32
4H	2H	2.68	3.55	3.09	3.90	4.29	2.68	3.55	3.09	3.90	4.29
	3H	2.70	3.40	3.11	3.81	4.21	2.70	3.40	3.11	3.81	4.21
	4H	2.72	3.34	3.15	3.76	4.21	2.72	3.34	3.15	3.76	4.21
	6H	2.74	3.28	3.21	3.73	4.20	2.74	3.28	3.21	3.73	4.20
	8H	2.73	3.23	3.20	3.68	4.15	2.73	3.23	3.20	3.68	4.15
	12H	2.70	3.14	3.19	3.62	4.10	2.70	3.14	3.19	3.62	4.10
8H	4H	2.60	3.10	3.08	3.55	4.03	2.60	3.10	3.08	3.55	4.03
	6H	2.66	3.06	3.17	3.56	4.04	2.66	3.06	3.17	3.56	4.04
	8H	2.66	3.02	3.19	3.54	4.04	2.66	3.02	3.19	3.54	4.04
	12H	2.66	2.98	3.18	3.47	4.05	2.66	2.98	3.18	3.47	4.05
12H	4H	2.55	2.99	3.04	3.47	3.95	2.55	2.99	3.04	3.47	3.95
	6H	2.60	2.96	3.13	3.48	3.98	2.60	2.96	3.13	3.48	3.98
	8H	2.63	2.95	3.15	3.45	4.02	2.63	2.95	3.15	3.45	4.02

END OF REPORT