

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221387

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221387
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 2436 LIGHT ENGINE, BLACK SHADE, WIDE DISTRIBUTION.
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source: 6500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23130.2 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.19
Luminous Opening: Vertical Cylinder (Dia: 1.54' x H: 0.71')
CIE Type: Direct

Input Watts (W): 193.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221387

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221387

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85
3	100	92	86	82	97	91	85	81	88	84	80	86	82	79	83	80	77
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70
5	88	78	71	66	86	77	71	66	75	70	65	73	68	65	72	67	64
6	82	72	65	60	81	71	65	60	69	64	59	68	63	59	67	62	58
7	77	66	60	55	76	66	59	54	64	58	54	63	58	54	62	57	54
8	73	62	55	50	71	61	54	50	60	54	50	59	53	49	58	53	49
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45
10	64	53	47	42	63	53	47	42	52	46	42	51	46	42	50	45	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83920
5°	80055
10°	76670
15°	73908
20°	70799
25°	68005
30°	63028
35°	54411
40°	41397
45°	27099
50°	12552
55°	2269
60°	546
65°	320
70°	302
75°	284
80°	242
85°	149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 27099 cd/sqm

TEST NUMBER: P1221387

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1384.8	6.0
10°-20°	4040.8	17.5
20°-30°	6229.0	26.9
30°-40°	6674.6	28.9
40°-50°	4032.0	17.4
50°-60°	649.7	2.8
60°-70°	58.4	0.3
70°-80°	42.2	0.2
80°-90°	18.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11654.6	50.4
0°-40°	18329.2	79.2
0°-60°	23010.9	99.5
0°-90°	23130.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23130.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14554	
5°	14538	###
15°	14321	4041
25°	13604	6229
35°	10896	6675
45°	5267	4032
55°	414	650
65°	53	58
75°	41	42
85°	17	19
90°	0	

TEST NUMBER: P1221387

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	14553.5
2.5°	14534.2
5°	14538.3
7.5°	14509.9
10°	14444.9
12.5°	14393.1
15°	14321.0
17.5°	14176.9
20°	13994.1
22.5°	13811.4
25°	13604.3
27.5°	13232.7
30°	12663.2
32.5°	11905.8
35°	10895.6
37.5°	9618.4
40°	8199.1
42.5°	6772.7
45°	5267.1
47.5°	3818.3
50°	2374.7
52.5°	1167.5
55°	414.2
57.5°	163.5
60°	95.4
62.5°	64.0
65°	52.8
67.5°	48.7
70°	46.7
72.5°	43.7
75°	40.6
77.5°	36.5
80°	31.5
82.5°	24.4
85°	17.3
87.5°	11.2
90°	0.0

TEST NUMBER: P1221387

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-BLAK-08 (6500K_L32_Wide_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.92	2.07	1.28	2.38	2.70	0.92	2.07	1.28	2.38	2.70
	3H	1.20	2.21	1.59	2.55	2.91	1.20	2.21	1.59	2.55	2.91
	4H	1.41	2.35	1.82	2.70	3.09	1.41	2.35	1.82	2.70	3.09
	6H	1.62	2.47	2.04	2.84	3.24	1.62	2.47	2.04	2.84	3.24
	8H	1.68	2.49	2.12	2.88	3.29	1.68	2.49	2.12	2.88	3.29
	12H	1.71	2.48	2.14	2.86	3.29	1.71	2.48	2.14	2.86	3.29
4H	2H	0.81	1.75	1.22	2.10	2.49	0.81	1.75	1.22	2.10	2.49
	3H	1.25	2.01	1.67	2.41	2.82	1.25	2.01	1.67	2.41	2.82
	4H	1.57	2.24	2.01	2.66	3.11	1.57	2.24	2.01	2.66	3.11
	6H	1.91	2.48	2.37	2.93	3.40	1.91	2.48	2.37	2.93	3.40
	8H	2.01	2.54	2.48	2.99	3.47	2.01	2.54	2.48	2.99	3.47
	12H	2.07	2.54	2.56	3.03	3.50	2.07	2.54	2.56	3.03	3.50
8H	4H	1.60	2.13	2.07	2.58	3.06	1.60	2.13	2.07	2.58	3.06
	6H	2.02	2.46	2.53	2.96	3.44	2.02	2.46	2.53	2.96	3.44
	8H	2.18	2.57	2.71	3.09	3.59	2.18	2.57	2.71	3.09	3.59
	12H	2.30	2.65	2.82	3.15	3.72	2.30	2.65	2.82	3.15	3.72
12H	4H	1.58	2.04	2.07	2.53	3.01	1.58	2.04	2.07	2.53	3.01
	6H	2.01	2.40	2.54	2.92	3.42	2.01	2.40	2.54	2.92	3.42
	8H	2.21	2.56	2.73	3.06	3.63	2.21	2.56	2.73	3.06	3.63