

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504972

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504972
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-80)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26864.2 lumens
Efficiency: N/A
Efficacy: 134.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.15
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 200.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504972

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504972

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	86	76	69	64	84	75	69	64	73	67	63	71	66	62	70	65	62	60			
6	81	70	63	58	79	69	62	57	68	61	57	66	61	57	65	60	56	54			
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			
9	67	55	48	44	66	55	48	44	54	48	43	53	47	43	52	47	43	42			
10	63	52	45	40	62	51	45	40	50	44	40	49	44	40	49	43	40	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123155
5°	123078
10°	122420
15°	121901
20°	120695
25°	118505
30°	112858
35°	101472
40°	81409
45°	62298
50°	47421
55°	29930
60°	9665
65°	4709
70°	1268
75°	490
80°	604
85°	690

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 62298 cd/sqm

TEST NUMBER: P1504972

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1586.1	5.9
10°-20°	4522.8	16.8
20°-30°	6703.1	25.0
30°-40°	6943.9	25.8
40°-50°	4700.3	17.5
50°-60°	2079.6	7.7
60°-70°	294.0	1.1
70°-80°	26.0	0.1
80°-90°	8.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12812.0	47.7
0°-40°	19756.0	73.5
0°-60°	26535.9	98.8
0°-90°	26864.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	26864.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16784	
5°	16710	###
15°	16047	4523
25°	14637	6703
35°	11328	6944
45°	6004	4700
55°	2340	2080
65°	271	294
75°	17	26
85°	8	8
90°	0	

TEST NUMBER: P1504972

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	16784.1
2.5°	16744.4
5°	16709.7
7.5°	16604.7
10°	16430.4
12.5°	16240.8
15°	16047.1
17.5°	15783.0
20°	15456.8
22.5°	15088.8
25°	14637.2
27.5°	14059.2
30°	13320.1
32.5°	12431.1
35°	11328.1
37.5°	9927.3
40°	8499.1
42.5°	7182.0
45°	6003.5
47.5°	5002.4
50°	4154.2
52.5°	3260.2
55°	2339.6
57.5°	1402.8
60°	658.6
62.5°	429.2
65°	271.2
67.5°	140.7
70°	59.1
72.5°	28.5
75°	17.3
77.5°	16.3
80°	14.3
82.5°	11.2
85°	8.2
87.5°	4.1
90°	0.0

(END OF REPORT)