

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504973

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504973
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 2 - 32,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25846.7 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 200.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504973

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504973

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74		
4	93	84	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56		
7	76	66	58	54	75	65	58	53	63	57	53	62	57	53	61	56	52	51		
8	72	61	54	49	71	60	54	49	59	53	49	58	52	49	57	52	48	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141923
5°	141527
10°	140049
15°	136382
20°	127748
25°	115195
30°	97310
35°	79739
40°	65571
45°	54851
50°	50226
55°	32799
60°	13015
65°	6389
70°	1663
75°	490
80°	604
85°	690

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 55051 cd/sqm

TEST NUMBER: P1504973

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1820.8	7.0
10°-20°	5011.1	19.4
20°-30°	6463.0	25.0
30°-40°	5598.6	21.7
40°-50°	4235.7	16.4
50°-60°	2280.3	8.8
60°-70°	399.3	1.5
70°-80°	29.4	0.1
80°-90°	8.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13294.9	51.4
0°-40°	18893.5	73.1
0°-60°	25409.5	98.3
0°-90°	25846.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	25846.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19342	
5°	19214	###
15°	17953	5011
25°	14228	6463
35°	8902	5599
45°	5286	4236
55°	2564	2280
65°	368	399
75°	17	29
85°	8	8
90°	0	

TEST NUMBER: P1504973

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-BLAK-PS (6500K_L32_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	19341.9
2.5°	19273.6
5°	19214.5
7.5°	19054.4
10°	18796.5
12.5°	18445.8
15°	17953.4
17.5°	17229.6
20°	16360.0
22.5°	15387.5
25°	14228.4
27.5°	12889.9
30°	11485.1
32.5°	10155.7
35°	8901.8
37.5°	7790.6
40°	6845.6
42.5°	6021.9
45°	5285.8
47.5°	5068.7
50°	4399.9
52.5°	3515.0
55°	2563.9
57.5°	1584.2
60°	886.9
62.5°	596.4
65°	368.0
67.5°	183.5
70°	77.5
72.5°	32.6
75°	17.3
77.5°	16.3
80°	14.3
82.5°	11.2
85°	8.2
87.5°	4.1
90°	0.0

(END OF REPORT)