

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505112

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505112
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-87)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 35214.6 lumens
Efficiency: N/A
Efficacy: 147.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.31
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 239.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505112

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505112

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55		
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45		
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37		
10	60	48	40	36	58	47	40	36	46	40	35	45	39	35	44	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127041
5°	127370
10°	127796
15°	128986
20°	129640
25°	130602
30°	131475
35°	131001
40°	119938
45°	97618
50°	69563
55°	45206
60°	21269
65°	15807
70°	15560
75°	18368
80°	22725
85°	28212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 97618 cd/sqm

TEST NUMBER: P1505112

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1646.1	4.7
10°-20°	4792.9	13.6
20°-30°	7439.7	21.1
30°-40°	8986.4	25.5
40°-50°	7188.0	20.4
50°-60°	3195.5	9.1
60°-70°	951.9	2.7
70°-80°	678.9	1.9
80°-90°	335.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13878.6	39.4
0°-40°	22865.0	64.9
0°-60°	33248.5	94.4
0°-90°	35214.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	35214.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17314	
5°	17292	###
15°	16980	4793
25°	16131	7440
35°	14625	8986
45°	9407	7188
55°	3534	3196
65°	910	952
75°	648	679
85°	335	335
90°	0	

TEST NUMBER: P1505112

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	17313.6
2.5°	17294.9
5°	17292.5
7.5°	17244.5
10°	17151.9
12.5°	17067.6
15°	16979.7
17.5°	16815.6
20°	16602.4
22.5°	16369.2
25°	16131.4
27.5°	15856.1
30°	15517.4
32.5°	15121.4
35°	14624.6
37.5°	13683.8
40°	12521.5
42.5°	11047.6
45°	9407.2
47.5°	7718.9
50°	6093.8
52.5°	4708.9
55°	3533.7
57.5°	2410.1
60°	1449.3
62.5°	1058.0
65°	910.4
67.5°	796.7
70°	725.3
72.5°	685.4
75°	647.9
77.5°	604.6
80°	537.8
82.5°	451.1
85°	335.1
87.5°	176.9
90°	0.0

(END OF REPORT)