

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505287

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)

Issue Date: 7/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1505287  
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-110)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)  
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE  
SHADE, MEDIUM DISTRIBUTION  
LIGHT LEVEL 2 - 32,000 LUMENS  
Light Source:  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 29048.0 lumens  
Efficiency: N/A  
Efficacy: 145.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.13  
Luminous Opening: Circular (Dia: 1.43' x H: 0')  
CIE Type: Direct

Input Watts (W): 200.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1505287

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)

### Luminous Intensity Polar Plot





TEST NUMBER: P1505287

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 111 | 108 | 104 | 101 | 109 | 105 | 102 | 100 | 101 | 99  | 97  | 97  | 95  | 94  | 94  | 92  | 91  | 89  |  |  |
| 2   | 104 | 97  | 92  | 88  | 101 | 96  | 91  | 87  | 92  | 88  | 85  | 89  | 86  | 83  | 86  | 83  | 81  | 79  |  |  |
| 3   | 97  | 88  | 82  | 77  | 95  | 87  | 81  | 76  | 84  | 79  | 75  | 82  | 77  | 74  | 79  | 76  | 73  | 71  |  |  |
| 4   | 90  | 81  | 74  | 68  | 88  | 79  | 73  | 68  | 77  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 65  | 63  |  |  |
| 5   | 84  | 74  | 67  | 61  | 83  | 73  | 66  | 61  | 71  | 65  | 60  | 69  | 64  | 60  | 67  | 63  | 59  | 57  |  |  |
| 6   | 79  | 68  | 61  | 55  | 77  | 67  | 60  | 55  | 65  | 59  | 55  | 64  | 58  | 54  | 62  | 58  | 54  | 52  |  |  |
| 7   | 74  | 63  | 55  | 50  | 73  | 62  | 55  | 50  | 61  | 54  | 50  | 59  | 54  | 49  | 58  | 53  | 49  | 47  |  |  |
| 8   | 70  | 58  | 51  | 46  | 68  | 57  | 51  | 46  | 56  | 50  | 45  | 55  | 49  | 45  | 54  | 49  | 45  | 43  |  |  |
| 9   | 66  | 54  | 47  | 42  | 64  | 53  | 47  | 42  | 52  | 46  | 42  | 51  | 46  | 42  | 50  | 45  | 41  | 40  |  |  |
| 10  | 62  | 50  | 43  | 39  | 61  | 50  | 43  | 39  | 49  | 43  | 39  | 48  | 42  | 38  | 47  | 42  | 38  | 37  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 116420 |
| 5°  | 116374 |
| 10° | 115938 |
| 15° | 115915 |
| 20° | 115417 |
| 25° | 114454 |
| 30° | 110134 |
| 35° | 94129  |
| 40° | 72761  |
| 45° | 53253  |
| 50° | 34808  |
| 55° | 20630  |
| 60° | 17505  |
| 65° | 16751  |
| 70° | 18730  |
| 75° | 20836  |
| 80° | 22873  |
| 85° | 24424  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 53253 cd/sqm

TEST NUMBER: P1505287

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 1650.3  | 5.7       |
| 10°-20°   | 4735.1  | 16.3      |
| 20°-30°   | 7123.6  | 24.5      |
| 30°-40°   | 7132.9  | 24.6      |
| 40°-50°   | 4382.5  | 15.1      |
| 50°-60°   | 1765.6  | 6.1       |
| 60°-70°   | 1077.3  | 3.7       |
| 70°-80°   | 842.2   | 2.9       |
| 80°-90°   | 338.5   | 1.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 13508.9 | 46.5      |
| 0°-40°    | 20641.9 | 71.1      |
| 0°-60°    | 26790.0 | 92.2      |
| 0°-90°    | 29048.0 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 29048.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 17452 |      |
| 5°  | 17378 | ###  |
| 15° | 16784 | 4735 |
| 25° | 15550 | 7124 |
| 35° | 11558 | 7133 |
| 45° | 5645  | 4382 |
| 55° | 1774  | 1766 |
| 65° | 1061  | 1077 |
| 75° | 808   | 842  |
| 85° | 319   | 338  |
| 90° | 0     |      |

TEST NUMBER: P1505287

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-06-WHGL-PS (6500K\_L32\_Medium\_120V)

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 17451.9 |
| 2.5°  | 17408.0 |
| 5°    | 17378.5 |
| 7.5°  | 17275.5 |
| 10°   | 17115.5 |
| 12.5° | 16963.6 |
| 15°   | 16784.1 |
| 17.5° | 16553.7 |
| 20°   | 16258.1 |
| 22.5° | 15942.1 |
| 25°   | 15549.6 |
| 27.5° | 15015.4 |
| 30°   | 14297.7 |
| 32.5° | 13048.9 |
| 35°   | 11558.5 |
| 37.5° | 9954.9  |
| 40°   | 8355.4  |
| 42.5° | 6912.9  |
| 45°   | 5644.7  |
| 47.5° | 4492.7  |
| 50°   | 3354.0  |
| 52.5° | 2319.2  |
| 55°   | 1773.8  |
| 57.5° | 1518.0  |
| 60°   | 1312.0  |
| 62.5° | 1144.8  |
| 65°   | 1061.2  |
| 67.5° | 1007.2  |
| 70°   | 960.3   |
| 72.5° | 894.1   |
| 75°   | 808.4   |
| 77.5° | 709.5   |
| 80°   | 595.4   |
| 82.5° | 465.9   |
| 85°   | 319.1   |
| 87.5° | 161.1   |
| 90°   | 0.0     |

(END OF REPORT)