

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505104

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505104
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 24,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24805.5 lumens
Efficiency: N/A
Efficacy: 155.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.17
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 159.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505104

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505104

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90		
2	104	98	93	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	78	74	79	76	73	71		
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	79	68	60	55	77	67	60	54	65	59	54	63	58	54	62	57	53	51		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	38	60	49	42	38	48	42	38	47	42	37	46	41	37	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103940
5°	103937
10°	103636
15°	103467
20°	102868
25°	101642
30°	97984
35°	89518
40°	73044
45°	57053
50°	44710
55°	30939
60°	14823
65°	11608
70°	9963
75°	11292
80°	13501
85°	15836

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57053 cd/sqm

TEST NUMBER: P1505104

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1340.5	5.4
10°-20°	3841.7	15.5
20°-30°	5756.8	23.2
30°-40°	6120.4	24.7
40°-50°	4302.5	17.3
50°-60°	2148.6	8.7
60°-70°	682.9	2.8
70°-80°	418.5	1.7
80°-90°	193.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10939.1	44.1
0°-40°	17059.5	68.8
0°-60°	23510.6	94.8
0°-90°	24805.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24805.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14165	
5°	14111	###
15°	13620	3842
25°	12554	5757
35°	9994	6120
45°	5498	4303
55°	2418	2149
65°	669	683
75°	398	418
85°	188	193
90°	0	

TEST NUMBER: P1505104

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L24_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	14165.3
2.5°	14143.3
5°	14111.1
7.5°	14033.1
10°	13909.4
12.5°	13770.4
15°	13620.4
17.5°	13423.8
20°	13173.8
22.5°	12892.5
25°	12554.4
27.5°	12118.8
30°	11564.6
32.5°	10868.9
35°	9993.5
37.5°	8824.9
40°	7625.8
42.5°	6506.4
45°	5498.0
47.5°	4649.7
50°	3916.7
52.5°	3177.8
55°	2418.5
57.5°	1633.8
60°	1010.1
62.5°	815.2
65°	668.6
67.5°	544.9
70°	464.4
72.5°	427.1
75°	398.3
77.5°	366.9
80°	319.5
82.5°	259.3
85°	188.1
87.5°	103.4
90°	0.0

(END OF REPORT)