

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P22178-R2

Luminaire Tested: **C1NW30SML**

Issue Date: 3/3/2020

**Test Information**


Test Method: LM-79-08  
Report Number: P22178-R2  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: C1NW30SML  
Description: \*\*\*THIS IS A REVISION OF P22178 TO UPDATE CATALOG NUMBER\*\*\*COMBOLIGHT ONE LED SMALL, 3 LED UNIT FLOOD [ DISTRIBUTION.  
Light Source: (3) 3000K SMT LEDS  
XPG  
Ballast/Driver: (1) MAGTECH HIGH PERFECTION ELECTRONIC DRIVER  
LP1020-12-C700

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 391.3 lumens  
Efficiency: N/A  
Efficacy: 49.5 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.59  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (Ain): 0.06837  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: HR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P22178-R2  
CATALOG NUMBER: C1NW30SML

### Luminous Intensity Polar Plot





TEST NUMBER: P22178-R2  
 CATALOG NUMBER: C1NW30SML

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	91	95	92	90	93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	89	87	85	84
5	98	92	87	84	97	91	87	83	89	86	83	88	85	82	86	84	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77
7	92	84	80	76	91	84	79	76	83	79	76	81	78	75	80	77	75	74
8	89	81	76	73	87	80	76	73	80	75	73	79	75	72	78	74	72	71
9	86	78	73	70	85	78	73	70	77	73	70	76	72	70	75	72	69	68
10	83	75	71	67	82	75	70	67	74	70	67	73	70	67	73	69	67	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	228929
5°	213295
10°	179467
15°	144155
20°	104776
25°	52987
30°	16965
35°	6692
40°	3435
45°	2171
50°	1365
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P22178-R2  
 CATALOG NUMBER: C1NW30SML

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.2	22.3
10°-20°	174.1	44.5
20°-30°	103.0	26.3
30°-40°	18.5	4.7
40°-50°	5.5	1.4
50°-60°	2.1	0.5
60°-70°	0.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.4	93.1
0°-40°	382.8	97.8
0°-60°	390.5	99.8
0°-90°	391.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	391.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1044	
5°	969	87
15°	635	174
25°	219	103
35°	25	18
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P22178-R2  
CATALOG NUMBER: C1NW30SML

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1044
2.5°	1021
5°	969
7.5°	893
10°	806
12.5°	721
15°	635
17.5°	546
20°	449
22.5°	337
25°	219
27.5°	123
30°	67
32.5°	40
35°	25
37.5°	17
40°	12
42.5°	9
45°	7
47.5°	5
50°	4
52.5°	3
55°	2
57.5°	2
60°	1
62.5°	1
65°	1
67.5°	1
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)