

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1505111

Luminaire Tested: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1505111
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 2436 LIGHT ENGINE, DOMIC WHITE
SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 36,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 33109.9 lumens
Efficiency: N/A
Efficacy: 138.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.02
Luminous Opening: Circular (Dia: 1.37' x H: 0')
CIE Type: Direct

Input Watts (W): 239.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1505111

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1505111

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	78	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	60	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52		
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164507
5°	164376
10°	163029
15°	159807
20°	151003
25°	138068
30°	118818
35°	98844
40°	82028
45°	69947
50°	64909
55°	45821
60°	24158
65°	17963
70°	14127
75°	15445
80°	18221
85°	20121

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 69947 cd/sqm

TEST NUMBER: P1505111

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2116.0	6.4
10°-20°	5877.9	17.8
20°-30°	7755.5	23.4
30°-40°	6924.5	20.9
40°-50°	5364.4	16.2
50°-60°	3184.0	9.6
60°-70°	1061.5	3.2
70°-80°	575.6	1.7
80°-90°	250.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	15749.3	47.6
0°-40°	22673.8	68.5
0°-60°	31222.2	94.3
0°-90°	33109.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	33109.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22420	
5°	22317	###
15°	21037	5878
25°	17054	7755
35°	11035	6924
45°	6741	5364
55°	3582	3184
65°	1035	1061
75°	545	576
85°	239	251
90°	0	

TEST NUMBER: P1505111

CATALOG NUMBER: PRLX-UHBS2-2436-MV-L8C5-U-A-04-WHGL-PS (6500K_L36_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	22419.7
2.5°	22371.7
5°	22316.6
7.5°	22144.3
10°	21880.7
12.5°	21533.9
15°	21037.1
17.5°	20277.9
20°	19338.2
22.5°	18306.0
25°	17053.5
27.5°	15606.5
30°	14023.6
32.5°	12494.6
35°	11034.7
37.5°	9697.8
40°	8563.7
42.5°	7609.9
45°	6740.6
47.5°	6379.7
50°	5686.1
52.5°	4660.9
55°	3581.8
57.5°	2447.6
60°	1646.2
62.5°	1312.3
65°	1034.6
67.5°	803.8
70°	658.5
72.5°	590.5
75°	544.8
77.5°	499.1
80°	431.2
82.5°	343.3
85°	239.0
87.5°	123.0
90°	0.0

(END OF REPORT)