

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P21910-R2

Luminaire Tested: **C1NW30MED**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P21910-R2
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: C1NW30MED
Description: ***THIS IS A REVISION OF P21910 TO UPDATE CATALOG NUMBER***COMBOLIGHT ONE LED MEDIUM, 7 LED UNIT FLOOD DISTRIBUTION, 3000K
.---ABSOLUTE PHOTOMETRY IS BASED ON CALIBRATION FACTORS CREATED USING A 500 WATT, NIST TRACEABLE, AND OMNI-DIRECTIONAL LAB LUMEN STANDARD IN THE GONIOPHOTOMETER WITH TEST DISTANCE OF 28.75 FEET---
Light Source: (7) SMT LEDS
XPG
Ballast/Driver: (1) MAGTECH ELECTRONIC DRIVER
LPT-1020-24-C0700


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 902.7 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.37 / 0.37 / 0.41
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 17.5
Input Voltage (V): NR
Input Current (Ain): 0.1471
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P21910-R2
CATALOG NUMBER: C1NW30MED

Luminous Intensity Polar Plot





TEST NUMBER: P21910-R2
 CATALOG NUMBER: C1NW30MED

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96				96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92				92
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89				89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86				86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83				83
6	97	91	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80				80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78				78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75				75
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	73				73
10	86	79	75	72	86	79	75	72	78	75	72	78	74	72	77	74	72	71				71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	458677
5°	389796
10°	259392
15°	155873
20°	82437
25°	37011
30°	16527
35°	8136
40°	4564
45°	2781
50°	2040
55°	1524
60°	1311
65°	1034
70°	639
75°	422
80°	0
85°	0



TEST NUMBER: P21910-R2
 CATALOG NUMBER: C1NW30MED

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.6	33.1
10°-20°	380.8	42.2
20°-30°	154.3	17.1
30°-40°	41.8	4.6
40°-50°	14.9	1.6
50°-60°	7.6	0.8
60°-70°	3.9	0.4
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.8	92.4
0°-40°	875.5	97.0
0°-60°	898.0	99.5
0°-90°	902.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4198	
5°	3554	299
15°	1378	381
25°	307	154
35°	61	42
45°	18	15
55°	8	8
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P21910-R2
CATALOG NUMBER: C1NW30MED

CANDELA DISTRIBUTION (FULL):

0°	
0°	4198
1°	4155
2°	4064
3°	3931
4°	3759
5°	3554
6°	3326
7°	3083
8°	2827
9°	2576
10°	2338
11°	2115
12°	1908
13°	1716
14°	1541
15°	1378
17.5°	1013
20°	709
22.5°	473
25°	307
27.5°	200
30°	131
32.5°	88
35°	61
37.5°	43
40°	32
42.5°	24
45°	18
47.5°	14
50°	12
52.5°	10
55°	8
57.5°	7
60°	6
62.5°	5
65°	4
67.5°	3
70°	2
72.5°	1
75°	1
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0



TEST NUMBER: P21910-R2
CATALOG NUMBER: C1NW30MED

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0}$

(END OF REPORT)