

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P22187-R2

Luminaire Tested: **C1NM30SML**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P22187-R2
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: C1NM30SML
Description: ***THIS IS A REVISION OF P22187 TO UPDATE CATALOG
NUMBER***COMBOLIGHT ONE LED SMALL, 3 LED UNIT NARROW FLOOD
DISTRIBUTION, 3000K
Light Source: (3) 3000K SMT LEDS
XPG
Ballast/Driver: (1) MAGTECH HIGH PERFECTION ELECTRONIC DRIVER
LP1020-12-C700


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 384.2 lumens
Efficiency: N/A
Efficacy: 46.3 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 8.3
Input Voltage (V): NR
Input Current (Ain): 0.07098
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: HR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P22187-R2
CATALOG NUMBER: C1NM30SML

Luminous Intensity Polar Plot





TEST NUMBER: P22187-R2
 CATALOG NUMBER: C1NM30SML

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 |
| 2 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99 | 101 | 99 | 97 | 99 | 97 | 95 | 96 | 94 | 93 | 91 |
| 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 92 | 90 | 93 | 91 | 89 | 88 |
| 4 | 102 | 96 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 91 | 89 | 86 | 90 | 87 | 85 | 84 |
| 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 |
| 6 | 95 | 88 | 84 | 80 | 94 | 88 | 83 | 80 | 86 | 83 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 78 |
| 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 77 | 83 | 79 | 76 | 82 | 79 | 76 | 81 | 78 | 76 | 75 |
| 8 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 79 | 75 | 73 | 72 |
| 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 69 |
| 10 | 84 | 76 | 72 | 69 | 83 | 76 | 72 | 69 | 75 | 71 | 68 | 74 | 71 | 68 | 74 | 70 | 68 | 67 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 260067 |
| 5° | 240369 |
| 10° | 193272 |
| 15° | 143247 |
| 20° | 89374 |
| 25° | 40889 |
| 30° | 16965 |
| 35° | 10708 |
| 40° | 2576 |
| 45° | 0 |
| 50° | 3753 |
| 55° | 2294 |
| 60° | 877 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 2516 |



TEST NUMBER: P22187-R2
 CATALOG NUMBER: C1NM30SML

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 97.2 | 25.3 |
| 10°-20° | 170.7 | 44.4 |
| 20°-30° | 85.4 | 22.2 |
| 30°-40° | 20.2 | 5.3 |
| 40°-50° | 5.3 | 1.4 |
| 50°-60° | 3.2 | 0.8 |
| 60°-70° | 0.5 | 0.1 |
| 70°-80° | 1.3 | 0.3 |
| 80°-90° | 0.3 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 353.3 | 92.0 |
| 0°-40° | 373.6 | 97.2 |
| 0°-60° | 382.1 | 99.5 |
| 0°-90° | 384.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 384.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1186 | |
| 5° | 1092 | 97 |
| 15° | 631 | 171 |
| 25° | 169 | 85 |
| 35° | 40 | 20 |
| 45° | 0 | 5 |
| 55° | 6 | 3 |
| 65° | 0 | 0 |
| 75° | 0 | 1 |
| 85° | 1 | 0 |
| 90° | 0 | |



TEST NUMBER: P22187-R2
CATALOG NUMBER: C1NM30SML

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|------|
| 0° | 1186 |
| 1° | 1175 |
| 2° | 1173 |
| 3° | 1130 |
| 4° | 1120 |
| 5° | 1092 |
| 6° | 1057 |
| 7° | 1018 |
| 8° | 986 |
| 9° | 923 |
| 10° | 868 |
| 11° | 827 |
| 12° | 780 |
| 13° | 728 |
| 14° | 666 |
| 15° | 631 |
| 17.5° | 504 |
| 20° | 383 |
| 22.5° | 269 |
| 25° | 169 |
| 27.5° | 112 |
| 30° | 67 |
| 32.5° | 47 |
| 35° | 40 |
| 37.5° | 9 |
| 40° | 9 |
| 42.5° | 15 |
| 45° | 0 |
| 47.5° | 3 |
| 50° | 11 |
| 52.5° | 1 |
| 55° | 6 |
| 57.5° | 1 |
| 60° | 2 |
| 62.5° | 0 |
| 65° | 0 |
| 67.5° | 1 |
| 70° | 0 |
| 72.5° | 4 |
| 75° | 0 |
| 77.5° | 1 |
| 80° | 0 |
| 82.5° | 0 |
| 85° | 1 |
| 87.5° | 0 |



TEST NUMBER: P22187-R2
CATALOG NUMBER: C1NM30SML

CANDELA DISTRIBUTION (continued):

90° | ———— 0°
 0

(END OF REPORT)