

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152590

Luminaire Tested: **AVS-E01-LED-E-U-SL4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152590
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E01-LED-E-U-SL4
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2954.1 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.3 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

Luminous Intensity Polar Plot



REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	613.2	0.0	613.2
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	2340.9	0.0	2340.9
	% Fixture	79.2	0.0	79.2
Total	Lumens	2954.1	0.0	2954.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	2.0
10°-20°	161.2	5.5
20°-30°	238.6	8.1
30°-40°	301.6	10.2
40°-50°	341.1	11.5
50°-60°	485.4	16.4
60°-70°	903.9	30.6
70°-80°	414.3	14.0
80°-90°	49.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2954.1	100.0
0°-180°	2954.1	100.0

Coefficient of Utilization



REPORT NUMBER: P152590


CATALOG NUMBER: AVS-E01-LED-E-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	269.0	9.1			
FM	(30°-60°)	865.5	29.3			
FH	(60°-80°)	1169.9	39.6			G1/1800
FVH	(80°-90°)	36.5	1.2			G1/100
BL	(0°-30°)	189.7	6.4	B1/500		
BM	(30°-60°)	262.5	8.9	B1/1000		
BH	(60°-80°)	148.3	5.0	B1/500		G1/500
BVH	(80°-90°)	12.7	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4
2.5°	640.0	641.7	639.7	639.4	639.4	639.0	637.0	636.7	634.0	634.3	635.0
5°	644.7	645.3	644.0	643.6	643.0	641.7	640.0	638.0	636.0	634.0	632.3
7.5°	649.3	648.7	647.7	647.7	646.6	644.7	641.3	638.7	634.3	632.0	629.0
10°	656.0	655.0	653.7	653.0	651.3	648.3	643.6	640.0	634.7	629.9	625.0
12.5°	662.4	662.0	660.0	659.0	656.4	653.4	647.7	642.0	635.0	627.7	621.0
15°	673.7	672.3	670.4	668.3	664.0	660.0	651.3	644.7	634.7	625.0	614.7
17.5°	693.4	691.0	689.0	684.7	679.4	672.3	659.7	648.3	634.7	620.6	609.0
20°	729.3	724.4	721.7	716.0	706.6	694.0	674.3	656.0	635.6	617.6	602.0
22.5°	769.9	766.6	763.0	759.4	744.7	726.3	699.7	672.3	641.7	616.4	596.4
25°	815.6	811.3	809.3	803.0	789.3	768.3	732.0	694.0	655.3	621.7	596.4
27.5°	856.4	855.0	854.7	847.4	834.3	809.6	766.6	721.0	674.0	632.6	601.3
30°	893.4	892.0	891.3	887.4	872.3	843.0	796.4	745.0	694.3	648.0	610.7
32.5°	932.6	928.3	926.3	918.7	901.7	867.4	814.0	760.6	710.4	663.0	621.0
35°	964.7	961.0	957.0	946.0	922.0	881.3	821.7	766.0	716.7	671.3	626.3
37.5°	988.0	984.4	978.7	964.7	935.0	886.0	821.3	764.4	714.3	670.1	627.4
40°	998.3	994.7	988.7	971.0	937.3	883.3	815.0	756.7	707.4	663.0	623.3
42.5°	994.3	991.7	984.0	967.0	929.9	871.3	802.4	742.4	694.0	651.7	614.3
45°	979.0	977.0	969.6	951.7	913.4	852.0	783.6	724.4	678.0	637.6	602.4
47.5°	956.0	955.3	948.0	930.4	892.3	832.6	764.4	706.6	662.0	624.0	592.3
50°	930.7	927.4	923.6	907.4	872.6	816.0	750.4	695.6	653.0	619.0	588.0
52.5°	914.7	913.7	910.4	895.6	862.4	806.3	744.0	691.7	652.3	618.0	585.7
55°	1056.7	1059.0	1028.3	964.7	908.7	833.0	763.0	712.0	668.7	634.0	610.4
57.5°	1563.0	1552.6	1500.0	1373.7	1231.0	1042.7	907.0	824.7	771.0	777.0	789.0
60°	1821.0	1819.0	1809.3	1760.3	1665.3	1522.0	1363.0	1180.6	1122.7	1129.0	1133.7
62.5°	1936.4	1939.4	1946.6	1928.3	1903.3	1861.7	1782.4	1709.0	1631.3	1602.4	1524.7
65°	1989.6	1995.0	2011.7	2022.0	2031.7	2039.0	2070.4	2156.4	2213.0	2107.0	1860.3
67.5°	1879.4	1905.0	1960.0	2013.7	2061.7	2129.9	2236.0	2435.6	2574.7	2444.4	2086.6
70°	1369.9	1405.0	1468.0	1634.0	1811.3	1966.3	2171.7	2475.6	2685.3	2584.7	2142.7
72.5°	859.0	868.7	896.7	957.6	1089.3	1288.3	1647.4	2103.3	2345.3	2265.0	1811.0
75°	545.0	548.3	547.4	561.3	583.6	627.0	769.0	1242.4	1606.6	1481.3	1009.3
77.5°	324.7	329.6	331.7	336.0	346.6	362.0	373.7	422.7	673.7	654.0	366.3
80°	272.0	276.0	272.6	271.7	265.0	260.3	266.0	260.3	241.7	232.6	214.3
82.5°	144.0	143.6	142.7	152.3	172.0	187.4	199.0	196.4	177.6	151.3	128.3
85°	79.0	81.7	81.7	85.0	82.0	82.4	85.0	89.6	83.0	69.3	56.7
87.5°	6.6	10.4	8.3	10.4	14.0	9.9	9.6	9.6	8.3	6.0	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4
2.5°	633.4	632.6	631.3	630.4	630.4	628.7	627.7	627.0	626.6	625.3	625.3
5°	631.3	629.0	626.6	625.0	624.0	622.4	619.7	618.3	616.7	615.3	614.7
7.5°	627.0	622.7	619.0	616.4	613.0	610.4	607.0	604.0	601.0	599.7	599.0
10°	620.3	614.7	609.0	604.0	599.4	594.7	590.4	586.0	582.4	579.7	577.0
12.5°	614.0	605.3	598.0	590.7	583.3	577.6	571.7	565.3	560.0	555.0	553.7
15°	605.3	595.3	586.0	577.0	568.0	558.7	551.3	544.4	535.6	529.9	525.7
17.5°	597.3	585.3	574.0	563.3	552.3	542.7	531.7	522.4	513.7	505.0	498.7
20°	588.7	575.6	563.6	551.7	539.7	527.4	514.7	502.7	492.0	481.7	471.3
22.5°	581.0	567.7	556.0	543.0	529.6	515.6	501.0	486.0	473.7	460.3	448.3
25°	576.4	561.7	549.6	537.0	522.4	507.0	490.4	472.6	457.6	442.4	428.0
27.5°	576.4	557.3	545.0	532.3	517.3	501.0	482.7	463.3	446.3	429.3	411.7
30°	581.3	558.0	541.3	528.0	512.6	495.0	474.7	454.3	435.6	415.6	398.7
32.5°	586.0	559.4	538.7	521.7	504.0	486.6	466.0	444.4	423.6	404.7	386.6
35°	589.0	559.4	533.7	512.0	492.0	475.0	454.7	433.0	412.0	393.4	376.7
37.5°	589.3	556.7	525.7	501.0	480.0	462.4	443.0	422.7	402.7	385.3	371.3
40°	586.0	551.3	517.6	489.3	467.4	449.3	431.7	413.4	395.3	381.0	369.0
42.5°	580.0	545.7	510.1	480.0	457.0	438.3	422.0	406.3	390.7	378.3	368.3
45°	571.0	538.0	503.0	474.3	451.7	432.0	416.0	403.0	389.6	379.4	369.3
47.5°	563.0	535.3	505.3	478.0	454.3	434.0	417.6	406.6	396.4	389.3	375.6
50°	561.3	534.0	506.3	481.0	457.0	436.4	422.0	416.4	413.4	409.0	388.0
52.5°	556.7	533.7	513.7	499.7	484.4	474.7	459.7	465.0	461.7	446.3	408.3
55°	605.7	612.3	631.0	657.6	682.4	688.0	686.3	680.0	646.3	556.0	457.3
57.5°	832.6	870.4	905.7	921.3	919.4	901.7	889.0	863.3	814.7	704.7	554.0
60°	1148.0	1154.0	1135.3	1107.7	1061.0	1022.0	980.3	932.3	861.7	754.0	613.4
62.5°	1438.3	1357.6	1274.7	1196.7	1125.7	1063.6	1005.7	938.7	846.6	734.3	605.7
65°	1643.3	1472.6	1341.7	1229.6	1129.3	1042.7	970.4	883.3	779.7	678.3	561.3
67.5°	1749.0	1487.4	1286.3	1130.4	988.0	868.0	771.7	687.0	609.9	565.7	491.3
70°	1631.0	1262.4	982.4	806.0	635.6	509.6	402.7	338.0	315.6	357.6	372.0
72.5°	1215.3	821.7	584.4	452.0	346.3	276.0	211.7	166.3	135.3	142.0	184.4
75°	574.7	354.7	250.7	190.7	151.7	125.7	102.7	94.0	78.7	65.3	61.3
77.5°	223.6	163.0	134.7	98.7	70.1	56.4	48.0	46.3	47.4	46.0	45.3
80°	170.4	115.3	72.3	53.0	45.7	40.3	35.6	34.3	35.0	36.7	38.3
82.5°	95.0	59.4	44.0	38.3	34.3	29.3	26.6	24.7	25.0	27.0	30.7
85°	36.7	28.7	26.3	25.3	23.6	19.0	16.4	16.7	19.0	22.7	22.7
87.5°	4.0	4.0	5.3	4.0	4.0	4.0	3.6	4.4	4.7	6.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4	630.4
2.5°	624.7	624.7	624.7	624.0	624.4	623.0	623.0	622.0	623.6	622.7	622.4
5°	615.0	614.7	613.4	613.4	613.4	613.4	614.3	611.7	613.7	613.7	612.6
7.5°	598.7	598.7	595.0	597.0	596.4	597.3	598.7	597.3	599.4	600.6	599.7
10°	576.0	576.0	573.0	575.3	574.3	576.7	579.0	577.6	579.0	581.0	581.7
12.5°	551.0	549.6	547.0	548.0	548.0	549.3	550.4	552.0	553.7	556.4	557.6
15°	522.0	520.0	516.7	516.7	514.7	515.3	517.3	518.0	521.3	525.0	529.3
17.5°	492.3	487.4	483.6	479.4	476.0	478.7	481.0	482.7	485.3	491.0	494.0
20°	464.4	454.3	447.4	441.7	438.0	439.7	442.7	444.7	447.0	448.3	449.3
22.5°	436.7	425.3	415.6	408.7	402.7	404.4	403.0	402.0	403.6	399.4	399.0
25°	412.6	399.4	386.3	378.0	370.7	368.3	361.3	359.7	355.0	351.3	348.7
27.5°	395.3	378.0	363.6	354.0	342.4	333.7	324.7	315.6	310.7	304.7	301.7
30°	381.7	363.3	346.3	329.9	314.7	301.3	289.3	277.6	269.6	261.0	255.3
32.5°	369.0	352.0	331.3	309.0	288.3	273.4	257.6	244.4	231.7	220.3	212.0
35°	360.3	341.3	315.0	287.7	264.4	246.6	230.1	211.0	195.6	181.0	172.0
37.5°	355.6	332.3	300.0	269.6	243.6	223.6	203.0	181.0	162.4	148.7	135.0
40°	352.0	323.3	286.6	253.7	226.3	202.4	178.3	152.3	131.7	117.3	106.6
42.5°	348.0	313.4	275.0	241.0	210.7	182.7	153.7	126.0	106.3	96.4	91.7
45°	343.6	304.7	264.0	229.0	195.3	161.3	128.0	102.4	90.7	87.4	87.4
47.5°	342.7	299.0	256.0	217.3	178.0	136.7	104.4	88.3	85.0	85.7	87.0
50°	346.6	297.3	249.0	203.6	155.0	110.7	88.3	83.0	83.6	85.7	87.7
52.5°	356.4	298.7	241.7	184.7	127.7	91.3	81.7	81.3	83.3	86.3	88.3
55°	372.6	298.7	227.7	156.4	102.0	82.0	79.4	80.6	83.3	86.0	87.7
57.5°	407.7	295.6	203.0	125.0	85.3	78.7	78.7	80.3	82.7	85.3	86.6
60°	449.3	291.7	168.3	96.7	77.0	76.0	78.3	80.3	82.4	84.7	86.0
62.5°	452.0	281.3	133.4	80.0	72.6	74.3	78.0	80.6	81.3	83.0	84.7
65°	415.3	245.3	106.0	71.7	70.7	73.4	77.0	79.0	79.4	80.0	81.7
67.5°	363.6	200.0	85.7	67.7	68.7	71.7	73.7	75.3	76.4	78.0	78.3
70°	298.7	160.6	73.4	63.6	64.7	68.0	69.6	71.3	73.4	75.3	74.3
72.5°	211.7	125.0	64.4	59.4	60.6	63.6	65.7	67.0	68.7	70.7	69.3
75°	89.9	87.4	55.6	53.7	55.6	57.6	59.7	61.7	63.3	64.4	64.4
77.5°	46.0	51.3	48.0	48.0	49.3	51.3	53.0	55.0	56.0	57.0	58.3
80°	39.0	39.7	40.3	41.7	43.0	45.0	46.6	48.3	48.7	49.0	49.6
82.5°	32.3	33.7	34.3	36.4	37.3	38.0	39.0	39.0	39.7	39.7	38.7
85°	23.3	25.0	26.0	26.3	26.0	26.3	26.6	27.4	29.0	29.0	27.7
87.5°	6.6	6.3	8.0	8.3	9.0	10.4	11.7	14.0	14.7	15.3	15.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152590

CATALOG NUMBER: AVS-E01-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	630.4	630.4	630.4	630.4
2.5°	622.0	622.7	621.3	621.7
5°	612.6	614.0	612.3	614.3
7.5°	600.6	602.7	602.4	602.0
10°	583.3	586.0	586.0	587.0
12.5°	561.3	563.0	564.4	565.0
15°	531.7	534.7	536.4	536.4
17.5°	496.0	498.0	499.0	497.6
20°	450.7	449.9	450.4	447.0
22.5°	398.3	399.4	396.4	397.0
25°	347.0	345.3	346.6	344.7
27.5°	297.3	297.6	294.0	295.6
30°	249.9	248.3	243.6	246.0
32.5°	204.4	200.0	195.0	192.0
35°	161.3	154.7	152.3	151.3
37.5°	126.6	119.4	117.0	114.3
40°	100.6	98.0	97.0	97.6
42.5°	90.4	90.4	91.0	91.3
45°	87.7	88.7	89.6	89.9
47.5°	88.0	89.0	90.4	90.7
50°	88.7	89.6	90.7	91.0
52.5°	89.0	89.0	89.6	89.9
55°	88.3	88.0	88.3	88.7
57.5°	87.0	86.3	86.6	87.7
60°	86.3	85.3	86.0	86.6
62.5°	84.7	84.4	85.0	85.3
65°	81.0	81.3	82.4	82.4
67.5°	77.6	78.0	78.3	78.7
70°	73.7	74.0	74.7	75.0
72.5°	69.0	70.4	71.3	72.6
75°	65.3	66.6	68.7	70.1
77.5°	59.0	60.0	62.4	64.0
80°	49.9	49.6	49.9	51.0
82.5°	38.3	38.3	38.0	37.6
85°	27.0	26.6	25.7	25.7
87.5°	14.7	14.3	14.0	13.4
90°	0.0	0.0	0.0	0.0

(END OF REPORT)