

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150890

Luminaire Tested: **AVS-E02-LED-E-U-SL3-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P150890
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-SL3-HSS
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (42) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3467.6 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G1

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.7 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	75.1	0.0	75.1
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	3392.5	0.0	3392.5
	% Fixture	97.8	0.0	97.8
Total	Lumens	3467.6	0.0	3467.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.7	0.3
10°-20°	49.7	1.4
20°-30°	107.1	3.1
30°-40°	228.8	6.6
40°-50°	506.1	14.6
50°-60°	857.6	24.7
60°-70°	1144.4	33.0
70°-80°	504.1	14.5
80°-90°	58.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3467.6	100.0
0°-180°	3467.6	100.0

Coefficient of Utilization



REPORT NUMBER: P150890


CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	144.8	4.2			
FM	(30°-60°)	1559.5	45.0			
FH	(60°-80°)	1632.4	47.1			G1/1800
FVH	(80°-90°)	55.7	1.6			G1/100
BL	(0°-30°)	23.7	0.7	B0/110		
BM	(30°-60°)	33.0	1.0	B0/220		
BH	(60°-80°)	16.1	0.5	B0/110		G0/110
BVH	(80°-90°)	2.3	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type III Short





REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7
2.5°	132.0	131.3	128.7	128.7	124.7	122.0	118.7	115.3	115.3	114.7	114.0
5°	174.7	170.7	169.9	162.7	156.7	148.0	140.0	129.3	128.0	126.6	126.0
7.5°	222.0	221.3	215.3	206.6	194.7	178.7	162.7	145.3	142.7	141.3	138.7
10°	283.3	280.0	272.0	257.3	239.4	218.0	192.0	164.7	161.3	158.7	157.3
12.5°	342.0	336.0	331.3	312.6	289.9	258.7	227.4	188.0	185.3	182.0	176.7
15°	396.7	391.3	383.3	367.4	342.0	302.7	266.0	218.0	211.3	206.6	202.7
17.5°	439.4	436.0	426.6	408.7	381.3	346.6	302.7	248.7	243.3	237.3	230.1
20°	480.0	475.3	460.6	436.0	406.6	380.0	346.0	288.7	281.3	274.0	266.0
22.5°	518.7	514.0	489.9	449.3	418.0	406.6	394.7	334.0	322.7	316.7	308.7
25°	572.6	562.7	525.3	460.6	418.7	427.4	448.0	392.6	382.0	373.4	360.6
27.5°	645.3	632.0	573.4	477.3	421.3	449.9	509.3	464.0	452.6	442.7	428.7
30°	727.4	718.7	648.7	517.3	440.6	483.3	578.0	554.7	541.3	529.3	512.6
32.5°	809.9	798.0	728.7	593.4	492.6	548.0	664.0	660.0	642.7	631.3	613.4
35°	882.7	876.7	825.3	718.0	611.3	661.3	778.7	783.3	768.0	756.0	736.0
37.5°	932.0	932.0	922.0	852.0	800.0	837.3	947.4	948.0	932.6	905.3	895.3
40°	957.3	964.7	1000.6	1014.0	1011.3	1059.4	1168.7	1156.7	1144.0	1129.9	1096.7
42.5°	1009.3	1016.0	1092.6	1184.7	1244.7	1308.0	1383.3	1379.4	1364.0	1338.7	1308.0
45°	1097.3	1106.0	1197.3	1343.3	1466.6	1556.7	1604.7	1586.0	1570.7	1546.6	1530.7
47.5°	1209.3	1226.0	1329.3	1509.9	1658.7	1807.4	1857.3	1808.0	1794.7	1776.0	1750.1
50°	1328.7	1344.7	1454.7	1661.3	1829.3	2006.6	2089.9	2006.6	1987.4	1981.3	1952.0
52.5°	1432.0	1445.3	1551.3	1778.0	1960.0	2168.0	2289.3	2179.4	2165.3	2145.3	2124.0
55°	1493.4	1504.0	1603.3	1834.0	2048.7	2313.4	2482.0	2385.3	2364.7	2356.7	2326.0
57.5°	1514.0	1524.7	1614.0	1841.3	2096.7	2446.0	2716.0	2719.4	2694.7	2666.0	2656.7
60°	1514.0	1526.0	1601.3	1823.3	2143.3	2587.4	3028.0	3306.0	3252.6	3247.4	3213.4
62.5°	1451.3	1462.7	1538.7	1768.0	2206.0	2778.0	3462.7	3953.4	3938.0	3903.3	3847.4
65°	1315.3	1322.0	1396.7	1626.6	2182.0	2953.4	3839.4	4384.0	4359.4	4291.3	4219.4
66°	1254.0	1259.4	1329.3	1546.0	2103.3	2977.3	3906.0	4438.0	4397.3	4340.0	4258.7
67.5°	1165.3	1174.7	1224.0	1396.0	1914.7	2894.0	3864.0	4400.0	4364.7	4295.3	4214.0
70°	778.0	771.3	945.3	1071.3	1458.7	2358.0	3466.6	3950.7	3951.3	3918.7	3886.0
72.5°	369.3	373.4	424.0	659.4	954.7	1575.3	2759.4	3153.4	3198.7	3140.0	3099.4
75°	265.3	271.3	302.0	403.3	569.3	945.3	1788.7	2205.3	2206.6	2102.7	2009.9
77.5°	77.3	80.6	113.4	248.7	426.6	638.0	1027.4	1226.0	1197.3	1122.7	1052.6
80°	32.0	32.0	33.4	79.4	171.3	433.4	718.7	944.0	940.6	912.0	870.7
82.5°	12.0	12.6	16.0	32.6	40.6	106.6	479.4	819.4	817.3	776.7	747.4
85°	1.3	1.3	4.0	14.0	15.3	20.0	96.0	361.3	359.4	361.3	316.7
87.5°	0.0	0.0	0.6	1.3	2.0	2.7	4.0	14.0	15.3	14.7	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7
2.5°	114.0	112.6	112.6	112.0	112.0	112.0	111.3	110.7	110.7	110.1	109.3
5°	124.7	123.3	122.7	121.3	120.6	120.0	118.7	118.0	116.7	116.0	115.3
7.5°	137.3	134.7	134.0	132.0	129.9	128.7	127.4	125.3	124.0	121.3	120.6
10°	153.4	150.1	147.4	144.7	142.7	139.4	137.3	134.7	132.0	129.9	128.0
12.5°	174.0	169.3	165.3	162.7	158.0	154.0	150.1	148.0	142.7	140.0	136.7
15°	196.7	191.3	186.6	181.3	178.0	171.3	166.0	160.0	157.3	152.6	147.4
17.5°	226.0	217.3	209.9	204.7	198.0	191.3	185.3	179.4	171.3	166.0	159.4
20°	257.3	249.9	240.0	230.7	222.7	214.7	206.0	198.0	190.7	182.0	174.0
22.5°	297.3	286.6	274.7	265.3	254.7	246.0	234.0	223.3	211.3	200.0	190.7
25°	348.0	334.0	322.7	309.3	296.7	283.3	268.7	255.3	240.0	229.3	213.4
27.5°	410.7	397.3	382.0	364.7	352.0	332.0	312.6	296.0	278.0	261.3	243.3
30°	490.7	471.3	455.3	438.7	413.4	394.0	371.3	348.7	324.0	307.4	280.0
32.5°	586.6	566.0	542.0	518.0	494.7	467.4	439.4	411.3	384.0	353.4	325.3
35°	704.0	679.4	652.0	626.0	590.1	560.6	525.3	486.6	456.0	420.6	385.3
37.5°	859.4	818.7	794.7	767.4	718.7	678.7	639.4	600.6	546.6	509.3	459.4
40°	1054.0	1030.1	990.7	946.6	902.7	849.9	796.7	745.3	682.7	630.7	572.6
42.5°	1282.7	1247.4	1207.4	1144.0	1099.4	1037.3	976.7	908.7	832.0	765.3	697.3
45°	1497.3	1455.3	1424.7	1361.3	1314.7	1241.3	1168.0	1096.0	1007.4	921.3	842.7
47.5°	1729.3	1694.7	1644.0	1592.6	1545.3	1462.7	1383.3	1296.0	1202.7	1100.6	998.7
50°	1933.4	1906.0	1871.3	1809.3	1756.7	1687.4	1594.0	1498.7	1380.6	1279.4	1163.3
52.5°	2106.6	2085.3	2036.7	1992.6	1945.3	1880.0	1796.7	1705.3	1578.0	1466.6	1334.7
55°	2311.3	2296.0	2253.4	2226.0	2184.0	2121.3	2043.3	1958.7	1824.0	1702.7	1553.4
57.5°	2646.6	2634.7	2597.3	2586.0	2544.7	2489.9	2394.0	2303.3	2146.0	1995.3	1824.7
60°	3202.0	3178.0	3123.3	3095.3	3008.0	2934.7	2809.9	2685.3	2495.3	2303.3	2098.0
62.5°	3796.7	3729.3	3625.3	3536.0	3412.0	3284.7	3118.0	2927.4	2704.7	2476.7	2240.6
65°	4117.3	4002.7	3871.3	3729.3	3568.7	3381.3	3171.3	2942.7	2703.3	2462.7	2213.4
66°	4154.0	4024.7	3885.3	3727.4	3548.7	3349.3	3136.0	2896.0	2647.4	2412.6	2163.3
67.5°	4108.0	3972.6	3825.3	3649.9	3456.7	3249.9	3026.0	2776.7	2537.3	2299.4	2056.7
70°	3786.0	3651.3	3520.0	3335.3	3129.3	2921.3	2709.3	2430.7	2204.0	1985.3	1769.3
72.5°	3023.3	2932.0	2802.0	2644.0	2443.3	2199.4	2022.7	1773.4	1576.7	1364.7	1197.3
75°	1889.3	1760.6	1600.0	1398.7	1245.3	1047.4	944.0	754.7	642.7	544.7	449.9
77.5°	966.0	869.3	756.7	643.3	534.7	426.6	329.9	233.4	157.3	109.3	81.3
80°	798.0	712.6	619.4	516.0	420.0	326.0	234.7	160.0	102.0	66.6	52.0
82.5°	659.4	587.4	504.0	408.0	324.7	256.0	178.0	116.0	72.0	46.6	36.7
85°	280.6	254.7	196.7	156.0	117.3	86.6	60.6	40.6	28.7	23.3	21.3
87.5°	12.0	13.4	12.6	9.9	7.4	7.4	6.6	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7	104.7
2.5°	109.3	108.7	108.0	108.0	107.4	106.6	102.7	99.4	95.3	92.6	89.9
5°	114.0	113.4	112.0	111.3	110.1	109.3	100.6	93.4	87.4	82.7	79.4
7.5°	118.7	118.0	116.0	114.0	113.4	112.0	98.0	88.7	80.6	75.3	72.0
10°	124.7	122.7	120.6	118.0	116.0	114.0	95.3	83.3	74.7	70.1	66.6
12.5°	133.4	129.9	126.6	123.3	120.6	117.3	94.0	78.7	70.1	64.7	61.3
15°	143.3	138.7	134.7	130.7	126.0	122.7	91.3	74.7	66.0	60.6	56.7
17.5°	152.6	147.4	141.3	135.3	130.7	126.0	88.7	70.7	62.0	56.7	52.6
20°	166.0	158.0	150.7	143.3	136.7	130.7	84.7	66.6	58.7	52.6	48.7
22.5°	180.6	171.3	162.0	152.0	143.3	135.3	81.3	63.3	55.3	49.3	44.7
25°	199.4	188.0	175.3	162.7	152.6	142.0	78.0	60.0	52.0	46.0	41.3
27.5°	225.3	209.3	195.3	179.4	164.0	152.0	75.3	57.3	48.7	42.7	38.0
30°	260.6	237.3	215.3	198.0	180.0	162.7	72.6	54.0	46.0	39.4	34.0
32.5°	300.0	272.6	247.4	221.3	198.7	178.7	70.1	51.3	42.7	36.0	31.3
35°	348.7	314.0	280.0	249.9	222.7	196.0	67.4	48.7	40.0	32.6	28.0
37.5°	418.7	375.3	330.7	292.0	256.7	221.3	65.3	46.0	36.7	29.3	24.7
40°	514.7	458.7	404.0	351.3	305.3	261.3	62.7	43.3	34.0	26.6	22.0
42.5°	618.7	550.7	478.7	419.4	356.0	300.6	60.0	40.6	31.3	24.0	19.4
45°	748.0	663.3	576.0	495.3	418.0	346.6	57.3	38.0	28.0	21.3	16.7
47.5°	889.3	781.3	682.7	581.3	489.3	404.0	54.0	36.0	25.3	18.7	14.7
50°	1034.7	920.6	796.0	680.6	571.3	461.3	50.7	32.6	22.7	16.7	12.0
52.5°	1191.3	1056.7	929.3	786.0	658.7	536.7	47.4	30.1	20.6	14.7	9.9
55°	1390.7	1240.0	1090.7	929.9	776.7	624.0	44.0	26.6	18.0	12.6	8.0
57.5°	1641.3	1462.7	1279.4	1098.0	912.0	738.7	41.3	23.3	15.3	10.7	6.6
60°	1878.0	1669.3	1447.4	1238.7	1028.7	826.6	37.3	20.6	13.4	8.7	6.6
62.5°	2000.6	1762.7	1523.3	1293.4	1069.3	858.0	33.4	17.3	11.3	7.4	6.0
65°	1970.7	1728.0	1496.0	1264.0	1044.7	838.0	29.3	15.3	9.9	6.6	6.0
66°	1927.4	1687.4	1454.0	1233.4	1024.0	816.7	27.4	14.7	9.3	6.6	5.3
67.5°	1832.6	1600.6	1378.0	1172.6	967.4	776.0	24.7	13.4	8.7	6.0	5.3
70°	1565.3	1354.7	1176.7	994.0	826.6	654.0	20.0	11.3	7.4	5.3	5.3
72.5°	1036.0	892.6	774.0	666.0	556.7	432.0	16.7	9.3	6.0	5.3	4.7
75°	390.7	353.4	303.3	272.6	238.0	208.7	13.4	6.0	4.7	4.7	4.7
77.5°	69.3	64.0	56.7	52.0	48.0	44.0	10.7	4.0	4.0	4.7	4.7
80°	46.6	43.3	39.4	36.0	33.4	30.1	7.4	3.3	4.0	4.0	4.7
82.5°	33.4	31.3	29.3	26.6	24.7	22.0	4.7	3.3	4.0	4.0	4.0
85°	20.0	18.7	17.3	16.0	14.0	13.4	3.3	3.3	3.3	4.0	4.0
87.5°	5.3	4.7	5.3	5.3	4.0	4.7	2.7	2.7	2.7	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150890

CATALOG NUMBER: AVS-E02-LED-E-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	104.7	104.7	104.7	104.7	104.7
2.5°	88.7	88.7	87.4	89.3	89.3
5°	76.7	76.7	76.0	76.7	76.7
7.5°	70.1	69.3	69.3	69.3	70.1
10°	64.0	63.3	63.3	63.3	63.3
12.5°	58.7	58.0	57.3	58.0	58.0
15°	54.0	52.6	52.6	52.6	52.6
17.5°	49.9	48.7	48.0	48.0	48.0
20°	46.0	44.0	44.0	44.0	44.0
22.5°	42.0	40.0	40.0	40.0	40.0
25°	38.0	36.0	36.0	36.0	36.0
27.5°	34.7	32.6	32.6	32.6	32.6
30°	30.7	29.3	29.3	30.1	29.3
32.5°	28.0	26.0	26.0	26.6	26.6
35°	24.7	23.3	23.3	23.3	23.3
37.5°	21.3	20.0	20.0	20.0	20.0
40°	18.7	17.3	16.7	17.3	17.3
42.5°	16.0	14.7	14.0	14.0	14.0
45°	14.0	12.0	11.3	12.0	12.0
47.5°	11.3	9.9	9.9	10.7	10.7
50°	8.7	8.7	9.3	10.7	10.7
52.5°	8.0	8.0	9.3	10.7	10.7
55°	7.4	8.0	9.3	9.9	10.7
57.5°	6.6	8.0	9.3	9.9	9.9
60°	6.6	7.4	8.7	9.9	9.9
62.5°	6.0	6.6	8.0	9.3	9.3
65°	6.0	6.6	8.0	9.3	9.3
66°	6.0	6.6	8.0	9.3	9.3
67.5°	6.0	6.6	8.0	9.3	9.3
70°	6.0	6.6	8.0	8.7	8.7
72.5°	5.3	6.0	7.4	8.7	8.7
75°	5.3	6.0	7.4	8.7	8.7
77.5°	5.3	6.0	7.4	8.7	8.7
80°	5.3	6.0	7.4	8.0	8.7
82.5°	4.7	6.0	6.6	8.0	8.0
85°	4.7	5.3	6.6	7.4	8.0
87.5°	4.0	4.7	5.3	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)