

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: SHAPER

Report Number: P237905

Luminaire Tested: **1400-DOME-80-L35-120**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P237905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25854)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: SHAPER
Catalog Number: 1400-DOME-80-L35-120
Description: SHAPER 1400 SERIES LED PENDANT DIRECT DOWNLIGHT
Light Source: LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 780.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 1.42 / 1.42 / 1.48
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 12.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P237905

CATALOG NUMBER: 1400-DOME-80-L35-120

Luminous Intensity Polar Plot





TEST NUMBER: P237905

CATALOG NUMBER: 1400-DOME-80-L35-120

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	77	74	71		
3	91	81	73	67	89	79	72	66	77	70	65	74	68	64	71	67	63	61		
4	84	72	63	57	81	71	63	57	68	61	56	66	60	55	64	59	54	52		
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45		
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40		
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	47	42	37	35		
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31		
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28		
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32132
5°	32564
10°	33091
15°	34044
20°	34679
25°	35290
30°	35906
35°	36500
40°	36486
45°	35515
50°	33025
55°	28924
60°	25113
65°	21919
70°	20088
75°	19635
80°	18966
85°	15426

TEST NUMBER: P237905

CATALOG NUMBER: 1400-DOME-80-L35-120

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.1	3.2
10°-20°	75.3	9.7
20°-30°	119.7	15.4
30°-40°	151.1	19.4
40°-50°	156.0	20.0
50°-60°	120.9	15.5
60°-70°	75.8	9.7
70°-80°	43.5	5.6
80°-90°	12.5	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.2	28.2
0°-40°	371.3	47.6
0°-60°	648.2	83.1
0°-90°	780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	263	25
15°	267	75
25°	259	120
35°	242	151
45°	204	156
55°	134	121
65°	75	76
75°	41	43
85°	11	13
90°	0	

TEST NUMBER: P237905

CATALOG NUMBER: 1400-DOME-80-L35-120

CANDELA DISTRIBUTION (FULL):

	0°
0°	260.5
2.5°	260.5
5°	263.0
7.5°	264.2
10°	264.2
12.5°	265.4
15°	266.6
17.5°	266.6
20°	264.2
22.5°	261.8
25°	259.3
27.5°	256.9
30°	252.1
32.5°	247.2
35°	242.4
37.5°	235.1
40°	226.6
42.5°	216.9
45°	203.6
47.5°	189.0
50°	172.1
52.5°	152.7
55°	134.5
57.5°	117.5
60°	101.8
62.5°	88.5
65°	75.1
67.5°	64.2
70°	55.7
72.5°	48.5
75°	41.2
77.5°	33.9
80°	26.7
82.5°	19.4
85°	10.9
87.5°	2.4
90°	0.0

(END OF REPORT)