

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: SHAPER

Report Number: P237909

Luminaire Tested: **1400-DOME-90-L35-120**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P237909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25854)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: SHAPER
Catalog Number: 1400-DOME-90-L35-120
Description: SHAPER 1400 SERIES LED PENDANT DIRECT DOWNLIGHT
Light Source: LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 690.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 1.42 / 1.42 / 1.48
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 12
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P237909

CATALOG NUMBER: 1400-DOME-90-L35-120

Luminous Intensity Polar Plot



TEST NUMBER: P237909

CATALOG NUMBER: 1400-DOME-90-L35-120

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	77	74	71			
3	91	81	73	67	89	79	72	66	77	70	65	74	68	64	71	67	63	61			
4	84	72	63	57	81	71	63	57	68	61	56	66	60	55	64	59	54	52			
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45			
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40			
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	47	42	37	35			
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31			
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28			
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28431
5°	28800
10°	29271
15°	30111
20°	30676
25°	31221
30°	31761
35°	32284
40°	32284
45°	31416
50°	29206
55°	25591
60°	22202
65°	19409
70°	17779
75°	17347
80°	16764
85°	13586

TEST NUMBER: P237909

CATALOG NUMBER: 1400-DOME-90-L35-120

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	3.2
10°-20°	66.6	9.7
20°-30°	105.9	15.4
30°-40°	133.7	19.4
40°-50°	138.0	20.0
50°-60°	106.9	15.5
60°-70°	67.0	9.7
70°-80°	38.4	5.6
80°-90°	11.1	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.8	28.2
0°-40°	328.5	47.6
0°-60°	573.4	83.1
0°-90°	690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	233	22
15°	236	67
25°	229	106
35°	214	134
45°	180	138
55°	119	107
65°	66	67
75°	36	38
85°	10	11
90°	0	

TEST NUMBER: P237909

CATALOG NUMBER: 1400-DOME-90-L35-120

CANDELA DISTRIBUTION (FULL):

	0°
0°	230.5
2.5°	230.5
5°	232.6
7.5°	233.7
10°	233.7
12.5°	234.8
15°	235.8
17.5°	235.8
20°	233.7
22.5°	231.6
25°	229.4
27.5°	227.3
30°	223.0
32.5°	218.7
35°	214.4
37.5°	208.0
40°	200.5
42.5°	191.9
45°	180.1
47.5°	167.2
50°	152.2
52.5°	135.1
55°	119.0
57.5°	104.0
60°	90.0
62.5°	78.3
65°	66.5
67.5°	56.8
70°	49.3
72.5°	42.9
75°	36.4
77.5°	30.0
80°	23.6
82.5°	17.2
85°	9.6
87.5°	2.1
90°	0.0

(END OF REPORT)