

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148620

Luminaire Tested: **AVS-E03-LED-E-U-5XQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148620
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-5XQ
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (63) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9541.1 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148620

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148620

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148620

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4770.6	0.0	4770.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4770.6	0.0	4770.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	9541.1	0.0	9541.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	0.9
10°-20°	254.9	2.7
20°-30°	426.8	4.5
30°-40°	650.6	6.8
40°-50°	1038.9	10.9
50°-60°	1597.3	16.7
60°-70°	2325.7	24.4
70°-80°	2619.9	27.5
80°-90°	540.8	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9541.1	100.0
0°-180°	9541.1	100.0

Coefficient of Utilization



REPORT NUMBER: P148620


CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	383.9	4.0			
FM	(30°-60°)	1643.4	17.2			
FH	(60°-80°)	2472.8	25.9			G2/5000
FVH	(80°-90°)	270.4	2.8			G3/500
BL	(0°-30°)	383.9	4.0	B1/500		
BM	(30°-60°)	1643.4	17.2	B2/2500		
BH	(60°-80°)	2472.8	25.9	B3/2500		G2/5000
BVH	(80°-90°)	270.4	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type V Short





REPORT NUMBER: P148620

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	904.0	904.0	904.0	904.0	904.0	904.0	904.0	904.0	904.0	904.0	904.0
2.5°	905.5	906.0	905.7	905.3	905.5	905.3	904.8	904.5	902.7	903.7	905.3
5°	905.5	905.0	904.8	904.5	904.5	905.3	904.6	903.7	903.5	904.0	903.2
7.5°	905.1	904.0	903.5	903.2	903.5	903.7	903.0	902.0	902.8	902.0	901.0
10°	903.4	902.8	903.0	902.0	902.3	902.0	901.0	900.3	900.7	900.0	898.8
12.5°	904.0	902.8	902.5	902.0	901.8	901.6	900.2	899.0	899.3	898.8	897.5
15°	904.0	903.2	903.0	902.0	901.8	901.2	899.8	899.3	899.3	898.4	897.0
17.5°	904.5	904.0	904.0	902.8	902.3	902.0	900.3	899.5	900.3	898.8	897.8
20°	905.9	905.5	905.7	905.1	904.0	903.9	902.8	902.3	902.5	902.3	899.5
22.5°	909.0	909.0	909.5	909.2	909.0	909.2	908.2	908.2	908.5	908.5	906.2
25°	917.5	917.3	917.7	917.7	918.0	919.8	919.0	918.8	920.0	920.0	917.7
27.5°	933.5	933.0	933.5	934.0	935.2	937.5	937.0	937.7	939.7	939.3	937.2
30°	952.0	951.5	952.7	954.3	955.2	958.8	957.2	961.0	962.7	964.2	962.8
32.5°	979.0	979.1	981.2	982.3	984.5	988.0	988.5	991.5	993.8	996.3	994.5
35°	1014.9	1014.5	1016.3	1018.0	1020.7	1024.0	1025.3	1029.2	1032.7	1034.5	1031.2
37.5°	1070.1	1067.3	1070.5	1071.5	1073.8	1074.5	1078.0	1083.0	1086.7	1086.2	1084.0
40°	1144.5	1143.9	1142.8	1141.2	1144.8	1146.0	1146.0	1152.7	1158.8	1157.7	1157.5
42.5°	1231.5	1229.2	1227.8	1227.8	1229.7	1230.3	1237.9	1243.0	1247.3	1248.3	1247.3
45°	1325.0	1322.7	1323.2	1322.3	1323.0	1326.2	1330.8	1340.0	1348.0	1348.2	1344.0
47.5°	1425.5	1418.4	1424.0	1416.3	1420.9	1423.5	1434.7	1448.3	1462.3	1464.8	1460.9
50°	1527.6	1526.7	1526.2	1524.8	1527.0	1532.5	1546.2	1567.5	1581.0	1590.1	1584.0
52.5°	1639.0	1635.2	1633.5	1631.0	1633.3	1643.9	1663.2	1681.8	1706.0	1716.3	1708.0
55°	1747.6	1746.3	1739.8	1739.5	1744.2	1761.0	1782.0	1804.8	1831.0	1842.5	1839.5
57.5°	1859.0	1851.7	1849.7	1846.8	1856.3	1872.0	1897.7	1938.8	1966.0	1979.1	1971.5
60°	1968.0	1962.5	1958.2	1957.3	1963.7	1985.7	2022.7	2072.0	2105.7	2122.8	2110.7
62.5°	2085.0	2081.5	2076.5	2070.8	2084.6	2112.7	2158.8	2213.3	2263.0	2284.0	2265.7
65°	2230.5	2223.2	2217.7	2210.5	2221.8	2257.2	2315.0	2391.7	2458.4	2483.0	2469.9
67.5°	2384.0	2377.2	2377.7	2373.3	2393.3	2442.5	2517.0	2621.2	2710.8	2752.5	2728.0
70°	2518.0	2521.8	2522.7	2541.0	2575.5	2650.5	2774.5	2937.8	3073.5	3137.2	3111.0
71°	2478.5	2486.8	2499.5	2518.5	2578.0	2666.7	2836.0	3033.8	3195.8	3303.7	3267.5
72.5°	2366.5	2371.5	2378.0	2407.0	2474.2	2591.7	2766.0	2991.9	3200.2	3340.0	3298.0
75°	2204.6	2209.2	2211.5	2231.7	2293.0	2395.4	2555.0	2755.5	2939.3	3058.2	3046.5
77.5°	1960.0	1960.7	1978.2	2009.5	2078.2	2195.4	2363.5	2571.5	2744.2	2836.8	2778.0
80°	1407.5	1398.0	1416.0	1456.3	1541.2	1675.8	1847.8	2085.3	2277.0	2363.5	2272.5
82.5°	535.5	564.6	610.3	676.7	705.5	854.9	1015.5	1155.0	1316.5	1497.0	1451.7
85°	57.5	64.8	81.2	100.7	127.3	176.0	243.2	332.0	409.2	481.0	427.0
87.5°	21.6	22.0	24.6	28.2	28.7	30.1	32.0	37.2	34.7	30.1	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148620

CATALOG NUMBER: AVS-E03-LED-E-U-5XQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	904.0	904.0	904.0	904.0	904.0	904.0	904.0	904.0
2.5°	904.0	904.2	904.0	904.2	904.2	903.2	903.5	903.0
5°	903.7	903.0	903.2	903.5	903.2	903.7	903.0	903.5
7.5°	902.5	901.0	901.6	901.6	901.0	901.8	901.2	900.9
10°	900.0	898.0	899.0	898.4	898.2	898.4	898.4	898.4
12.5°	897.7	896.6	896.8	896.5	896.3	897.0	896.8	897.0
15°	897.2	895.2	895.0	894.5	894.7	895.2	895.2	896.0
17.5°	896.8	894.3	894.0	893.5	893.8	894.7	895.0	894.5
20°	898.2	896.3	895.8	895.2	895.0	896.3	896.0	896.0
22.5°	905.3	902.8	902.5	900.5	899.8	900.5	900.0	900.0
25°	916.5	913.5	912.5	909.7	907.8	907.8	907.0	906.5
27.5°	936.7	932.2	931.2	929.0	926.2	926.7	925.3	925.0
30°	960.2	956.3	952.7	949.5	946.2	945.0	943.2	943.0
32.5°	991.1	986.5	982.2	978.2	973.8	972.0	969.0	967.5
35°	1028.8	1022.8	1017.8	1015.0	1010.5	1008.3	1006.2	1008.5
37.5°	1081.5	1074.2	1071.7	1068.5	1065.5	1062.0	1062.8	1062.0
40°	1154.5	1148.0	1145.5	1139.8	1139.0	1134.9	1137.5	1135.0
42.5°	1244.8	1232.7	1231.0	1226.5	1225.0	1222.7	1223.7	1222.0
45°	1343.0	1332.2	1330.3	1323.0	1323.2	1318.0	1320.0	1320.0
47.5°	1453.5	1442.3	1433.1	1427.8	1425.7	1422.5	1424.2	1424.0
50°	1567.5	1552.2	1542.0	1531.8	1527.3	1528.5	1525.0	1531.0
52.5°	1689.9	1667.3	1652.7	1643.0	1634.5	1636.3	1636.7	1638.5
55°	1816.8	1787.8	1766.7	1754.0	1746.2	1746.7	1749.0	1751.0
57.5°	1944.2	1908.0	1879.5	1860.5	1855.5	1857.7	1857.7	1857.4
60°	2076.5	2033.0	1996.3	1974.7	1970.3	1969.0	1978.8	1975.5
62.5°	2218.4	2166.2	2128.3	2100.7	2094.3	2098.8	2107.6	2105.5
65°	2406.7	2334.5	2285.5	2258.2	2247.3	2251.7	2263.5	2263.0
67.5°	2649.5	2548.5	2483.7	2448.7	2440.7	2446.2	2452.7	2459.1
70°	3012.4	2868.3	2775.8	2700.0	2667.5	2661.2	2667.8	2668.0
71°	3140.3	2974.5	2827.3	2734.7	2681.5	2659.0	2660.7	2649.5
72.5°	3135.0	2930.8	2758.5	2661.8	2587.8	2569.7	2561.0	2547.6
75°	2923.7	2739.7	2590.3	2484.8	2413.5	2392.2	2376.8	2376.0
77.5°	2651.5	2515.8	2351.0	2239.3	2152.5	2117.3	2101.6	2100.9
80°	2131.5	1928.3	1807.8	1740.5	1635.8	1605.5	1573.5	1561.5
82.5°	1289.0	1007.3	819.0	727.8	677.2	557.7	500.5	473.6
85°	300.3	213.3	146.9	96.5	69.5	55.2	42.5	37.5
87.5°	20.2	16.0	14.3	11.5	8.7	8.5	5.2	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)