

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148630

Luminaire Tested: **AVS-E04-LED-E-U-5XQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148630
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-5XQ
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (84) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12721.5 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3

Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148630

CATALOG NUMBER: AVS-E04-LED-E-U-5XQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148630

CATALOG NUMBER: AVS-E04-LED-E-U-5XQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148630

CATALOG NUMBER: AVS-E04-LED-E-U-5XQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6360.7	0.0	6360.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6360.7	0.0	6360.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	12721.5	0.0	12721.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.9	0.9
10°-20°	339.8	2.7
20°-30°	569.0	4.5
30°-40°	867.5	6.8
40°-50°	1385.2	10.9
50°-60°	2129.8	16.7
60°-70°	3101.0	24.4
70°-80°	3493.2	27.5
80°-90°	721.1	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12721.5	100.0
0°-180°	12721.5	100.0

Coefficient of Utilization



REPORT NUMBER: P148630


CATALOG NUMBER: AVS-E04-LED-E-U-5XQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	511.9	4.0			
FM	(30°-60°)	2191.2	17.2			
FH	(60°-80°)	3297.1	25.9			G2/5000
FVH	(80°-90°)	360.6	2.8			G3/500
BL	(0°-30°)	511.9	4.0	B2/1000		
BM	(30°-60°)	2191.2	17.2	B2/2500		
BH	(60°-80°)	3297.1	25.9	B4/5000		G2/5000
BVH	(80°-90°)	360.6	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short





REPORT NUMBER: P148630

CATALOG NUMBER: AVS-E04-LED-E-U-5XQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
2.5°	1207.4	1208.0	1207.7	1207.0	1207.4	1207.0	1206.3	1206.0	1203.7	1205.0	1206.9
5°	1207.4	1206.6	1206.3	1206.0	1206.0	1207.0	1206.0	1205.0	1204.7	1205.3	1204.4
7.5°	1206.6	1205.3	1204.7	1204.4	1204.7	1205.0	1204.0	1202.7	1203.7	1202.7	1201.3
10°	1204.8	1203.7	1204.0	1202.7	1203.0	1202.7	1201.3	1200.3	1201.0	1200.0	1198.3
12.5°	1205.4	1203.7	1203.3	1202.7	1202.4	1202.0	1200.3	1198.7	1199.0	1198.3	1196.7
15°	1205.4	1204.4	1203.9	1202.7	1202.4	1201.7	1199.6	1199.0	1199.0	1197.9	1196.0
17.5°	1206.0	1205.4	1205.4	1203.7	1203.0	1202.7	1200.3	1199.4	1200.3	1198.3	1197.0
20°	1208.0	1207.4	1207.7	1206.6	1205.3	1205.3	1203.6	1203.0	1203.3	1203.0	1199.4
22.5°	1212.0	1212.0	1212.6	1212.3	1212.0	1212.3	1211.0	1211.0	1211.3	1211.3	1208.3
25°	1223.3	1223.0	1223.7	1223.6	1224.0	1226.3	1225.3	1225.0	1226.7	1226.7	1223.6
27.5°	1244.7	1243.9	1244.7	1245.3	1247.0	1249.9	1249.3	1250.4	1253.1	1252.3	1249.6
30°	1269.3	1268.7	1270.3	1272.3	1273.7	1278.3	1276.4	1281.3	1283.7	1285.6	1283.6
32.5°	1305.3	1305.3	1308.3	1309.6	1312.6	1317.3	1318.0	1322.1	1325.0	1328.3	1326.0
35°	1353.4	1352.6	1355.0	1357.3	1361.0	1365.4	1367.0	1372.3	1377.0	1379.4	1375.0
37.5°	1426.6	1423.0	1427.4	1428.7	1431.7	1432.6	1437.3	1443.9	1449.0	1448.3	1445.4
40°	1526.0	1525.4	1523.7	1521.7	1526.3	1528.0	1528.0	1537.0	1545.0	1543.6	1543.3
42.5°	1642.1	1639.0	1637.0	1637.0	1639.7	1640.4	1650.7	1657.4	1663.0	1664.4	1663.0
45°	1766.6	1763.7	1764.4	1763.0	1764.0	1768.3	1774.3	1786.7	1797.3	1797.7	1792.0
47.5°	1900.6	1891.3	1898.7	1888.3	1894.6	1898.0	1913.0	1931.0	1949.6	1953.0	1948.0
50°	2036.7	2035.6	2035.0	2033.0	2036.0	2043.3	2061.7	2089.9	2108.0	2120.0	2112.0
52.5°	2185.3	2180.3	2178.0	2174.7	2177.6	2191.9	2217.6	2242.4	2274.6	2288.3	2277.3
55°	2329.9	2328.3	2319.7	2319.4	2325.6	2348.0	2376.0	2406.3	2441.3	2456.7	2452.6
57.5°	2478.7	2469.0	2466.3	2462.4	2475.0	2496.0	2530.4	2585.0	2621.3	2638.7	2628.6
60°	2624.0	2616.7	2611.0	2609.6	2618.3	2647.7	2697.0	2762.7	2807.7	2830.4	2814.3
62.5°	2780.0	2775.3	2768.7	2761.0	2779.3	2817.0	2878.3	2951.0	3017.3	3045.4	3020.9
65°	2974.1	2964.4	2957.0	2947.4	2962.3	3009.6	3086.6	3189.0	3278.0	3310.7	3293.4
67.5°	3178.7	3169.6	3170.4	3164.4	3191.0	3256.7	3356.1	3495.0	3614.3	3670.1	3637.3
70°	3357.4	3362.3	3363.7	3388.0	3434.0	3534.0	3699.3	3917.0	4098.0	4183.0	4148.0
71°	3304.7	3315.6	3332.6	3358.0	3437.3	3555.6	3781.3	4045.0	4260.9	4405.0	4356.7
72.5°	3155.3	3162.1	3170.7	3209.3	3299.1	3455.6	3688.0	3989.3	4266.9	4453.4	4397.3
75°	2939.4	2945.7	2948.7	2975.6	3057.3	3194.0	3406.6	3674.0	3919.0	4077.6	4062.0
77.5°	2613.3	2614.3	2637.7	2679.4	2771.0	2927.4	3151.3	3428.6	3659.0	3782.4	3704.0
80°	1876.7	1864.0	1888.0	1941.7	2054.9	2234.4	2463.6	2780.3	3036.1	3151.3	3030.1
82.5°	714.0	752.6	813.7	902.4	940.6	1140.0	1354.0	1540.0	1755.3	1996.1	1935.6
85°	76.7	86.3	108.4	134.3	169.6	234.7	324.4	442.7	545.7	641.3	569.3
87.5°	28.6	29.3	32.6	37.6	38.3	40.0	42.7	49.6	46.4	40.0	32.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148630

CATALOG NUMBER: AVS-E04-LED-E-U-5XQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
2.5°	1205.3	1205.6	1205.3	1205.7	1205.7	1204.4	1204.7	1203.9
5°	1205.0	1203.9	1204.4	1204.7	1204.4	1205.0	1203.9	1204.7
7.5°	1203.3	1201.3	1202.0	1202.0	1201.3	1202.3	1201.7	1201.2
10°	1200.0	1197.3	1198.7	1197.9	1197.7	1198.0	1198.0	1197.9
12.5°	1197.0	1195.3	1195.6	1195.3	1195.0	1196.0	1195.6	1196.1
15°	1196.4	1193.7	1193.4	1192.6	1193.0	1193.7	1193.7	1194.7
17.5°	1195.6	1192.3	1192.0	1191.3	1191.7	1193.0	1193.4	1192.6
20°	1197.7	1195.0	1194.3	1193.7	1193.3	1195.0	1194.6	1194.7
22.5°	1207.0	1203.7	1203.3	1200.6	1199.7	1200.7	1200.0	1200.0
25°	1222.0	1218.0	1216.7	1213.1	1210.4	1210.4	1209.3	1208.7
27.5°	1249.0	1243.0	1241.7	1238.7	1235.0	1235.6	1233.7	1233.4
30°	1280.3	1275.0	1270.4	1266.0	1261.7	1260.0	1257.6	1257.4
32.5°	1321.3	1315.3	1309.6	1304.4	1298.3	1296.0	1292.0	1289.9
35°	1371.7	1363.7	1357.0	1353.4	1347.4	1344.4	1341.7	1344.7
37.5°	1442.0	1432.3	1429.0	1424.7	1420.7	1416.0	1417.0	1416.0
40°	1539.4	1530.7	1527.3	1519.6	1518.7	1513.4	1516.7	1513.4
42.5°	1659.7	1643.6	1641.3	1635.3	1633.3	1630.4	1631.7	1629.3
45°	1790.7	1776.4	1773.7	1763.9	1764.4	1757.3	1760.0	1760.0
47.5°	1938.0	1923.0	1910.7	1903.6	1901.0	1896.7	1899.0	1898.7
50°	2089.9	2069.6	2056.0	2042.3	2036.4	2037.9	2033.4	2041.3
52.5°	2253.4	2223.0	2203.6	2190.7	2179.4	2181.7	2182.4	2184.7
55°	2422.3	2383.6	2355.6	2338.7	2328.3	2329.0	2332.0	2334.7
57.5°	2592.3	2544.0	2506.0	2480.6	2474.0	2477.0	2477.0	2476.7
60°	2768.7	2710.7	2661.7	2633.0	2626.9	2625.4	2638.3	2634.0
62.5°	2957.9	2888.3	2837.7	2801.0	2792.3	2798.3	2809.9	2807.4
65°	3209.0	3112.6	3047.4	3011.0	2996.4	3002.3	3018.0	3017.4
67.5°	3532.6	3397.9	3311.7	3265.0	3254.3	3261.7	3270.4	3278.7
70°	4016.7	3824.4	3701.0	3600.0	3556.7	3548.4	3557.0	3557.3
71°	4186.9	3966.0	3769.6	3646.3	3575.3	3545.3	3547.7	3532.6
72.5°	4180.0	3907.7	3678.0	3549.0	3450.4	3426.3	3414.7	3396.7
75°	3898.3	3653.1	3453.7	3313.0	3218.0	3189.6	3169.0	3168.0
77.5°	3535.3	3354.3	3134.7	2985.7	2869.9	2823.0	2802.1	2801.2
80°	2842.0	2571.0	2410.4	2320.7	2180.9	2140.6	2098.0	2082.1
82.5°	1718.7	1343.0	1092.0	970.4	903.0	743.6	667.4	631.3
85°	400.3	284.4	196.0	128.7	92.6	73.7	56.7	49.9
87.5°	27.0	21.3	19.0	15.3	11.6	11.4	7.0	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)